


Slip Ring Capsules (Compact)

AC7356** Specifications (IP 65 Sealed Version of AC6355)		Options	
Operating Speed	250 rpm*	<ul style="list-style-type: none"> 48 inch (1200 mm) length leads 50 ohm coax, RG178 75 ohm coax, RG179 	
Circuit Configurations	36 ring		56 ring
	36 @ 2 amp		56 @ 2 amp
	4 @ 5 amp; 28 @ 2 amp		4 @ 5 amp; 48 @ 2 amp
	4 @ 10 amp; 20 @ 2 amp		4 @ 10 amp; 40 @ 2 amp
Lead Length	24 inch (600 mm)		
Lead Size / Type	2 amp, 26 AWG 5 amp, 20 AWG 10 amp, 16 AWG		
Housing	Aluminum housing, black anodized		
Voltage	240 VAC		
Operating Temp.	-40°C to +80°C		
Contact Material	Gold		
Electrical Noise	60 milliohms max.		
Environmental	IP 65 sealed		

*Please note that the operational life of the unit is dependent upon rotational speed, environment and temperature.

**Product Replaced AC7038. Contact factory for details.

AC7356** Dimensions



Dimensions in inches