

INTEGRATED AVIONICS UNIT



Moog's Integrated Avionics Unit (IAU) offers solutions for Command and Data Handling/Electrical Power Subsystem (C&DH/EPS) for a full range of spacecraft and payload applications. Configurations include single string and redundant systems. The IAU leverages TRL-9 legacy heritage with options for tailoring and/or customized new designs to meet mission requirements. The IAU is optimized for orbit and radiation requirements and utilizes traditional EEE parts in Level-1, -2, and -3 part grades.

KEY CAPABILITIES

- Integrated C&DH and EPS Sub-System Functionality
- Supports all Sub-System Interfaces:
 - Telemetry, Tracking, & Command (TT&C)
 - Guidance, Navigation, & Control (GNC)
 - Payload
 - Power Distribution
 - Power (Solar Arrays and Batteries)
 - Propulsion
 - Thermal
 - Structures and Mechanisms
 - Launch Vehicle and Ground Support
- Modular and Scalable 3U Form Factor based Architecture
 - Single Board Computer (SBC) with Mission Specific I/O Boards
- SWaP (Dependent on # I/O Boards)
 - Size: Up to 25 x 21 x 12 cm
 - Mass: Up to 8.3kg
 - Power: Up to 37 W (IAU) and 3,000 W (System)

- Orbits: LEO GEO, Lunar, Interplanetary
- Mission Life
 - Single String: Up to 10 Years
 - Redundant: Up to 15 Years
- Environment: GEVS
- EEE Parts: Level 1, Level 2, Level 3
 - SEL Immune, SEU Mitigated Designs
- BRE440 SBC Based Processor Board
- Uplink Hardware Command Decode
- Variable Downlink Rates and formats (CCSDS, SGLS...)
- Flash or SDRAM based Mass Memory
- Battery Charge Management
- Robust Safety and Fault Interlocks
- Dead Bus Recovery / EOL Disposal Capability



INTEGRATED AVIONICS UNIT



IAU FEATURED SUMMARY

Feature	Specifications	Feature	Specifications
CPU	SBC with on-board memory	+28V Power Distribution	Solar Array Interface
	CPU Boot Memory (EEPROM, KB) - TMR		Battery Charge Management
	CPU System Memory (SDRAM, MB) - EDAC		Current Monitoring
	CPU FSW Storage (FLASH, GB) - TMR		28V Switch Over Current Trip
Payload Processing	Payload Processor Support		28V Arm/Fire Switches (7.0A)
Data Storage	IO Buffer Memory (SDRAM, MB)		28V Arm/Fire Switches (5.0A)
	IO Buffer Memory (SRAM, MB)		28V Arm/Fire Switches (2.0A)
	IO Buffer Memory (FLASH, GB) - TMR or ECC		28V Fire-Only Switches (50.0A)
Communication Interfaces	10/100/1000BaseT Ethernet		28V Fire-Only Switches (30.0A)
	MIL-STD-1553B		28V Fire-Only Switches (20.0A)
	SpaceWire		28V Fire-Only Switches (10.0A)
Digital IO	Total LVDS/RS-422 Transmitters		28V Fire-Only Switches (5.0A)
	Total LVDS/RS-422 Receivers		28V Fire-Only Switches (2.0A)
	Total CMOS Bi-Level Outputs		28V Fire-Only Switches (1.2A)
	Total CMOS Bi-Level Inputs		28V Thruster Driver Switches
	DeSerializers		28V HLD Switches (0.2A)
Analog IO	Analog Voltage Inputs (+/-10V)		28V H-Bridges (Torque Rods)
	AD590 Temperature Inputs		+5V Power Output (IMU Support)
	PRT/Thermistor Temperature Inputs		+/-15V Power Output (IMU Support)
	Coarse Sun Sensor Inputs		3-Phase Motor Control
GPS	GPS Receiver with dual inputs	+28V Power Distribution	28V EMI Filtering
			28V DC/DC Converter (+3V, +5V, ±15V)



2228 W. Guadalupe Road Gilbert. AZ 85233 www.moog.com/space

Moog Space and Defense

in

t @MoogSDG





Equipment described herein falls under the jurisdiction of the EAR and may require US Government Authorization for export purposes. Diversion contrary to US law is prohibited.

2021 Moog, Inc. All rights reserved.
Product and company names listed are trademarks or trade names of their respective companies.