MOOG | SPACE | PROPULSION | ELECTRIC PROPULSION ISOLATION VALVES

ISOLATION VALVES MONOPROPELLANT, SINGLE SEAT, LATCHING SOLENOID AND NORMALLY CLOSED SOLENOID



Moog supported high profile SDI programs such as SCIT, THAAD, ASAT and GBI/EKV by designing very small, light, fast-acting solenoid valves. Moog applied this technology from these programs to successfully develop and qualify a family of light-weight, high-pressure isolation valves for cold gas and high-purity xenon propellant management systems. The latch valves utilize permanent magnetics to hold the valve element in the last (open/closed) commanded

position. The solenoid valve is a normally closed design. These valve designs have been used in various space propulsion and operational systems in support of planetary and GEO satellite applications.

KEY ADVANTAGES

- All welded design to prevent external leakage
- Vespel[®] and stainless steel construction
- Inlet filter









ISOLATION VALVES

Characteristic

PERFORMANCE CHARACTERISTICS







	1/8 inch line, Latching Solenoid	1/4 inch line, Latching Solenoid	Normally Closed Solenoid
Max Operating Pressure, MEOP	2,700 psia (186 bar)	2,700 psia (186 bar)	2,700 psia (186 bar)
Proof Pressure	4,050 psia (279 bar)	6,000 psia (414 bar)	4,050 psia (279 bar)
Burst Pressure	8,100 psia (558 bar)	10,000 psia (689 bar)	6,750 psia (465 bar)
Flow vs. Pressure Drop	$< 15~\text{psid}$ (1 bar) at 20 slpm GN_{2} and 1,000 psia (69 bar) inlet, 70F	< 4.5 psid (0.31 bar) at 80 mg/s Xe and 50 psia (3.4 bar) inlet, 70F	<15 psid (1 bar) at 4.5 slpm $GN_{\rm 2}$ and 1000 psia (69 bar) inlet, 70F
Operating Voltage Range	22 to 42 Vdc	25 to 32 Vdc	26 to 52 Vdc, 8.6 hold open
Response Time	< 50 msec	< 75 msec	< 10 msec
Power Consumption	13.5 watts at 28 Vdc, 70F	10.6 watts at 28 Vdc, 70F	10.5 initial watts, 1 at hold voltage, 70F
Leakage, Internal	< 3 scc/hr GHe	< 3 scc/hr GHe	< 3 scc/hr GHe
Leakage, External	< 1E-6 scc/s GHe	< 1E-6 scc/s GHe	< 1E-6 scc/s GHe
Cycle Life	18,000 cycles	13,000 cycles	1,000,000 cycles
Weight	< 0.375 (170) lbm (g)	< 0.75 (340) lbm (g)	< 0.25 (115) lbm (g)
Inlet Filtration [micron absolute rating]	5	25	25
Operating Temperature Range	50 to 140 °F (10 to 60 °C))	14 to 151 °F (-10 to 66 °C))	-207 to 160 °F (-133 to 71 °C))
Back-EMF suppression Diodes	N/A	Available, 33Vdc clip	N/A
Representative Model Numbers	-051-212B	-051E311	-051E378



500 Jamison Road Plant 20, East Aurora, NY 14052 USA www.moog.com/space

f in @MoogSDG







Moog Space and Defense

Equipment described herein falls under the jurisdiction of the EAR and may require US Government Authorization for export purposes. Diversion contrary to US law is prohibited.

o 2022 Moog. Inc. All rights reserved. Product and company names listed are trademarks or trade names of their respective companies.