MOOG I SPACE I PROPULSION I HELIUM REGULATOR

HELIUM REGULATOR MECHANICAL PRESSURE REGULATOR



Moog model 50-1425 high flow pressure regulator is a series-redundant unit designed to provide stable tank pressure for propellant in a spacecraft propulsion system. Both regulator stages are temperature compensated and have inlet and outlet filters. The upstream regulator features a flow limiter. The design can be provided as a single-stage unit.









KEY FEATURES

- Nominal 250 psia regulated outlet
- Inlet pressures from 400 2500 psia
- Primary operation: upstream regulates with downstream open
- Each stage meets specified flow and pressure requirements
- Temperature-compensated
- Inlet and outlet filters
- First stage flow limiter


HELIUM REGULATOR

PERFORMANCE CHARACTERISTICS


Characteristics	Performance / Interfaces
Unit Weight	13.0 lbm max.
Dimensions	10.5 inch x 8.8 inch x 3.1 inch
Flow Rate (Operating)	1.2 - 24.5 SCFM (helium)
Maximum Flow Rate	50 SCFM (helium)
Surge Protection Flow Rate	< 4.0 SCFM (@ min. 20,000 psi/sec)
Internal Leakage	< 0.007 scc/sec (@ lock-up)
External Leakage	< 1x10 ⁻⁶ scc/sec
Temperature (Operating)	-40°F to 160°F
Cycle Life	1500 Cycles
MEOP (Inlet)	2500 psia
Regulated Pressure (Outlet)	250 psia (nominal)
Lock-up	260 psia (single stage)
Wetted Materials	Titanium, stainless steel, inconel

VARIANTS AVAILABLE

- 1. Single stage unit
- 2. No flow limiter
- 3. Regulation set point can be adjusted









For More Information: Bill Vogt bvogt@moog.com www.moog.com/space









@MoogSDG

Equipment described herein falls under the jurisdiction of the EAR and may require US Government Authorization for export purposes. Diversion contrary to US law is prohibited.

© 2022 Moog, Inc. All rights reserved. Product and company names listed are trademarks or trade names of their respective companies.