### PROPULSION | SINGLE LINE ISOLATION LATCH VALVES

# SINGLE LINE ISOLATION LATCH VALVES



Moog latch valves have been in production for more than four decades. The valves were originally developed for Galileo, LEASAT, INSAT, and Minuteman. The valves can be used for controlling propellants and pressurization gasses. The latch valves are bi-stable, and will stay in the last (open/closed) commanded position.





#### **KEY FEATURES**

- All welded design to prevent external leakage
- PTFE Seal and stainless steel or titanium construction
- Direct microswitch position indication
- Transition tubes available for stainless to titanium and titanium to stainless steel
- Inlet filter available for most configurations





## SINGLE LINE ISOLATION LATCH VALVES

#### PERFORMANCE CHARACTERISTICS

Characteristic









Valve	1/4 inch line, Torque Motor, Stainless Steel	3/8 inch line, Torque Motor, Stainless Steel	3/8 inch line, Torque Motor, Titanium	1/2 to 3/4 inch line, Linear Force Motor, Stainless Steel
Max Operating Pressure, MEOP [psia(bar)]	420 (28.9)	260 (17.9)	350 (24.1)	400 (27.5)
Proof Pressure [psia(bar)]	1155 (79.6)	600 (41.4)	500 (34.4)	900 (75.8)
Burst Pressure [psia(bar)]	2500 (172)	1600 (110)	2500 (172)	2000 (138)
Back Pressure Relief (BPR) [psid]	50-350	25 to 250 annular, 40 to 200 simple	25 to 200 annular, 250 to 550 simple	50 to 90
Max Delta P [H <sub>2</sub> 0]	4 psid at 0.01 lbm/s	3.5 psid at 0.175 lbm/s annular, 6 psid at 0.11 lbm/s simple	5 psid at 0.19 lbm/s annular, 19 psid at 0.1 lbm/s simple	11.2 psid at 0.71 lbm/s
Operating Voltage Range [Vdc]	22 to 34	18 to 51.5	24 to 34	24 to 32
Max Response Time [msec]	50	50	50	50
Power Consumption [watts]	20 at 28 Vdc, 70F	26 at 28 Vdc, 70F	14 at 34 Vdc, 70F	62 at 32 Vdc, 70F
Leakage, Internal [scc/hr GHe]	1	5	5	5
Leakage, External [scc/s GHe]	1E-6	1E-6	1E-6	1E-6
Cycle Life [cycles]	50,000	5,000	20,000	3,000
Mass [lbm (kg)]	0.72 (0.32)	1.54 (0.690)	1.76 (0.730)	4.3 (2.0)
Inlet Filtration [micron absolute rating]	40	None	40	40
Operating Temperature Range [°F (°C)]	-29 to 160 (-34 to 71)	14 to 150 (-10 to 66)	-29 to 160 (-34 to 71)	0 to 140 (-18 to 60)
Representative Model Numbers	51-181, 51-401	52-265, 52-220	52E252, 52-316	53-189, 53-334



500 Jamison Road Plant 20, East Aurora, NY 14052 USA www.moog.com/space









Equipment described herein falls under the jurisdiction of the EAR and may require US Government Authorization for export purposes. Diversion contrary to US law is prohibited.

© 2022 Moog, Inc. All rights reserved. Product and company names listed are trademarks or trade names of their respective companies.