


Hydraulic Distribution Manifold

Distribute hydraulic power to downstream devices



Product Overview

Moog Hydraulic Distribution Manifold (HDM) address to hydraulic power distribution for aerospace, automotive and other test systems. HDM connects in between a hydraulic power source, such as Hydraulic Service Manifold (HSM) or Hydraulic Power Unit (HPU), and downstream hydraulic devices, for example hydraulic actuators. It helps the test facilities layout the hydraulic circuitry in a simple and neat structure.

Features and Benefits


Features	Benefits
2 levels of flow rate design	Adaptable to different sizes of hydraulic source
280 or 210 bar system pressure	Used in high or low hydraulic power source system
Up to 8 outlet ports	Flexible selection for specific application
Quick coupling hydraulic fitting	Quick and easy to plug in/out the hydraulic hoses
Pilot pressure line available	Higher flexibility to supply pilot pressure for hydraulic devices

Typical Applications

Different models are designed for specific application, typically HDM can be used in

- Aero and static testing
- Dynamic and large flow system
- General piping and HPU splitting

Dimensions




Model	Outlet Qty	L (mm)	W (mm)	W1 (mm)	H (mm)
C050-51	4	582	422	320	400
	6	827	422	320	400
	8	1066	422	320	400
C050-52	4	755	614	320	450
	6	1075	614	320	450
C050-53	2	753	627	320	450

Specifications

C050-51


- **Rated flow:** 400 l/min
- **System pressure:** 280 bar
- **Application:** aero/static testing oriented
- **Inlet ports:**
 - P: 1-1/2", Code-62
 - R: -24, JIC-37°Flare
 - D: -6, JIC-37°Flare
 - PP: -6, JIC-37°Flare, or 1/4" Quick Coupling
- **Outlet ports:**
 - P: -12, JIC-37°Flare, or 1/2" Quick Coupling
 - R: -12, JIC-37°Flare, or 1/2" Quick Coupling
 - D: -6, JIC-37°Flare, or 1/4" Quick Coupling
 - PP: -6, JIC-37°Flare, or 1/4" Quick Coupling

Ordering Code




C050-52

- **Rated flow:** 880 l/min
- **System pressure:** 210 or 280 bar
- **Application:** dynamic/large flow
- **Inlet ports:**
 - P: 2", Code-62
 - R: 2", Code-61
 - D: -8, JIC-37°Flare, or DIN 24° Cone (12L)
 - PP: -6, JIC-37°Flare, or DIN 24° Cone (10L)
- **Outlet ports:**
 - P: -24, JIC-37°Flare, or DIN 24° Cone (38S)
 - R: -24, JIC-37°Flare, or DIN 24° Cone (38S)
 - D: -6, JIC-37°Flare, or DIN 24° Cone (10L)
 - PP: -6, JIC-37°Flare, or DIN 24° Cone (10L)



C050-53

- **Rated flow:** 880 l/min
- **System pressure:** 280 bar
- **Application:** piping and HPU splitting
- **Inlet ports:**
 - P: 2", Code-62
 - R: 2", Code-61
 - D: -12, JIC-37°Flare
 - PP: -6, JIC-37°Flare
- **Outlet ports:**
 - P: 2", Code-62
 - R: 2", Code-61
 - D: -8, JIC-37°Flare
 - PP: -6, JIC-37°Flare



Moog has offices around the world.
For more information or the office
nearest you, contact us online.

e-mail: info@moog.com

USA: +1 716 652 2000

The Netherlands: + 31 252 462 000

China: +86 21 2893 1600

www.moog.com

Moog is a registered trademark of Moog Inc. and its subsidiaries. All trademarks as indicated herein are the property of Moog Inc. and its subsidiaries. ©2020 Moog Inc. All rights reserved. All changes are reserved.

Hydraulic Distribution Manifold
MSH/PDF/Rev.A Nov 2020, CDL 59574

This technical data is based on current available information and is subject to change at any time by Moog. Specifications for specific systems or applications may vary.

MOOG