

WHAT MOVES YOUR WORLD



MOOG



WHAT HAPPENS WHEN YOU CONSIDER THE POSSIBILITIES INSTEAD OF THE LIMITATIONS?

It's time to overcome obstacles. Move out of your comfort zone. Listen to that little voice inside you. Start making your design ideas real. Put new projects in motion. It's time to join forces. Collaborate on what's next. And always look ahead. What moves your world? It's time to find out.





10,000+ EMPLOYEES. 25+ COUNTRIES. ONE MISSION.

Even if you don't know our name, you've still experienced what we can do. Moog motion control solutions are quietly at work in every corner of the globe, in a wide array of industrial applications where the highest level of performance is critical to world-class productivity. Our forward-thinking approach to expanding the limits of hydraulic, electric and hybrid control technologies has helped us to earn the confidence of today's most respected design engineers, manufacturing experts and machine builders in markets like plastics, metal forming, and beyond.

The power of collaboration

Despite the fact that Moog facilities operate in 25 countries around the world, our teams all speak a common language: helping our industrial customers take their ideas beyond what they thought possible. This mission extends throughout the larger Moog organization as well—an over 2 billion USD organization serving military and commercial aircraft, satellites, space and launch vehicles, missiles, industrial machinery, and medical applications.

By leveraging engineering breakthroughs from other areas and tapping into the key assets and expertise of the entire organization, our Industrial Group can offer a significant depth of intellectual capital and production capabilities.

60 years old and we're growing even stronger

Today, Moog is a respected product innovator and well-established organization with thousands of employees and a half-century of achievements and accolades. We're a public company listed on the New York Stock Exchange (NYSE Symbol: MOG.A and MOG.B). And we're setting new performance standards in world-class motion control solutions every day.

The true essence of our organization can be traced back to 1951 when founders Bill Moog, Art Moog, and Lou Geyer came together to form The Moog Valve Company around Bill's historic invention, the first practical servo valve—a high-performance control device that was more reliable and easier to build.

The collaborative spirit of these three ambitious pioneers lives today in our commitment to do whatever it takes to help customers address their unique challenges with expertise, advice and continually evolving product lines that help overcome their toughest obstacles.

TAKING YOUR VISION TO A HIGHER LEVEL

The pressure has never been greater on manufacturers to achieve greater efficiencies or higher productivity. To produce premium-quality products right off the machine. Or to incorporate new raw materials or manufacturing processes.

Likewise, the demands continue to grow on industrial equipment to work harder, faster, longer and at less cost. Depending on the machine, the application, the region or the budget constraints, the right motion control solution may be hydraulic. It may be electric. Or it may require a combination of both.

No matter what the technology, Moog's control electronics and software provide the brains for high performance and control. Best of all, it all works together seamlessly.

That's why Moog application engineers always start with the challenge, rather than the product. We ask the tough questions. Dig deeper. Take the initiative. And think more about the end result than providing pre-packaged answers on how to get there. This technology-neutral approach gives you the benefit of our best thinking and the high performance of our world-class product lines.

Hydraulic solutions

Since inventing the first practical servo valve in 1950, our name has been synonymous with hydraulic motion control technologies. Today, Moog Servo Valves, Proportional Valves, Servo Cartridges, Actuators and Radial Piston Pumps can be found in a myriad of applications. These include plastic injection and blow molding machines; metal forming presses; gas, steam

and wind turbines for power generation; controls on paper-making machinery and steel mill equipment; control systems on Formula One race cars; actuators on fatigue-test systems; and control of flight simulators, among others.

Electric solutions

Clean operation, less noise and low energy consumption are just a few elements that make electromechanical motion controls the ideal solution in many applications around the world. Motion control with electric technology is a more and more viable option for high performance applications due to the development of powerful servo motors, servo drives, actuators and electronics. Applications as diverse as plastics machinery, tube-bending machines, pitch systems for wind turbines, gas turbines, down-hole drilling and flight simulators all benefit from Moog expertise in this rapidly emerging technology.

Hybrid solutions

What if you could harness the best of both hydraulic and electric technologies in a single-unit closed-loop motion control solution for ultra high-end applications? These hybrid solutions—used in the subsea industry, for instance—are the newest frontier. By incorporating the advantages of existing technologies—including modular flexibility and increased efficiency and cleanliness—into revolutionary solutions, we're working hard to move beyond industry conventions to create more robust systems for tomorrow's machines.



PUTTING COLLABORATION IN MOTION IN MARKETS WORLDWIDE

How can we help you operate more productively?
More precisely? More economically?

By carefully analyzing your system requirements, your current technologies, your technical specifications and your overall performance objectives, and working together to help bring your ideas to life, we're making a real difference in today's most dynamic markets.

Energy Production and Generation Machinery

Wind Turbines

The motion control challenges for wind turbines are particularly complex, ranging from assuring efficiency to increasing reliability and safety. Moog offers OEMs and energy providers high performance solutions in key application areas: pitch systems, slip ring solutions, blade sensing and rotor monitoring systems. From pitch systems to hydraulic and electric products to service, we are a reliable partner to the world's leading wind turbine manufacturers. Moog solutions are in over 20,000 units in operation worldwide, with more being added every day.

Gas and Steam Turbines

Manufacturers of gas and steam turbines have relied on Moog motion control solutions for nearly two decades. While many customers still look at Moog for world-class hydraulic systems, increasingly engineers are turning to Moog for

electric solutions including fail-safe actuators, controllers and explosion-proof motors.

Oil and Gas Exploration

In downhole drilling applications for oil and gas exploration, Moog has developed actuators, motors and electronics able to withstand extreme temperatures in harsh conditions.

Industrial Production Machinery

Plastics Machinery

Today, Moog Proportional Valves, Radial Piston Pumps, Motion and Machine Controllers, Servo Drives, Servo Motors and related software play a key role all high-performance injection molding machines as OEMs strive to deliver higher productivity and thinner, lower-weight plastic parts using new materials and resins. Our high-performance products and systems provide precision control in injection and blow-molding machines used in automotive, packaging, electronics and medical industries, to name a few.

Steel, Aluminum and Paper Mills

Our solutions are employed in steel and aluminum mills around the world, providing position and gauge control that allow for higher productivity and superior quality of finished parts. Paper-making machines rely on Moog solutions for precision control in high-speed operations.



Metal Forming Machinery and Presses

Leading machine builders understand that with the right motion control solutions, they can achieve higher productivity, better precision and greater part-to-part consistency. From closed-loop cushion control on vertical stamping presses to closed-loop, high-performance solutions for press brakes to electric motion control solutions on bending, powder and punch presses, Moog continues to set the pace in this dynamic industry. What's more, our experts are continually working to develop new hybrid solutions for greater efficiencies and productivity in metal forming.

Test and Simulation Equipment

Test

New designs, shorter time-to-market, more complex and costly test subjects, and the quest for greater cost efficiencies mean test engineers in the aerospace and automotive markets require a new breed of technology partner with the right mix of solutions and expertise. Moog combines electric and hydraulic components and systems with flexibility and expertise to make today's automotive and aerospace tests more reliable and cost-effective. From turnkey machines to state-of-the-art controllers, software and components, we're helping customers shape the next generation of design with powerful test solutions that did not exist just a few years ago.

Simulation

Military and commercial aviators continually strive to improve their flying skills through flight simulation training. These cutting-edge simulators rely on Moog motion control solutions for a variety of critical functions. We design and build complete motion systems including large all-electric motion bases with a payload capacity of 14,500 kg (32,000 lbs.). Another Moog focus is designing the sophisticated control software that operates the bases and allows maintenance testing without additional test equipment. We offer control loading systems based on our unique force-loop technology and high performance Moog G-seats for smooth, reliable performance.

Other Markets

Motorsport

In Formula One motorsport, our high-performance servo valves provide the speed and power density critical to the world's top teams. In fact, we're continually pushing the boundaries of what's possible—designing sophisticated sub-miniature valves that are far lighter and fast acting with the same capabilities of much larger and heavier valves.

From our origins in closed-loop control to today's systems featuring software with embedded intelligence, Moog is poised to deliver motion control solutions for the next generation of high-performance machines. If you can imagine the possibilities, we'll help you achieve them.

BUILDING BETTER SOLUTIONS

For more than 60 years, Moog products have been specified for some of the world's most critical motion control applications. As new applications arise, our design teams work closely with customers to add new items to our extensive product rosters. Some are tailored for use in one-of-a-kind installations. Others become standard equipment on machines across many industries. These state-of-the-art products are continuously improved to take advantage of the latest technology breakthroughs and advancements. They are fundamental to the success of the high-performance motion control solutions we develop in collaboration with our customers.

Servo Valves and Proportional Valves



When Bill Moog invented the first practical servo valve, his name became synonymous with high performance, reliability and versatility. Moog Servo Valves today work in tandem

with other motion control products and use the latest technologies including fieldbus communication, embedded motion control electronics, and configuration software that incorporates advanced motion control algorithms

and interchangeability with open architecture systems. What's more, they can be found in a variety of specialized configurations including explosion-proof models and fail-safe versions for unique machine needs. Yet they remain the heart of the motion control system, critical to machine function, quality and productivity.

Servo Motors and Servo Drives

For more than 20 years, our brushless servo motor products have earned a reputation for dynamic



performance, power density and reliability in applications ranging from robotics, down-hole drilling, material handling, textiles, flight simulation, plastics and more. Through key acquisitions over the years, we've continually broadened our product range, always tailoring or modifying the specifications to fit our customers' needs. Actuators using our electric components provide high-performance, customized solutions for flight simulation, metal forming, blow molding and more.



Servo Actuators

Moog has developed an extensive range of hydraulic and electric actuators that is ideal for high performance applications. Our offering includes

world-class products as well as packages that combine electric linear servo actuators with servo drives and easy to use software. Known for long-lasting performance and reliability, Moog's actuators also offer easier installation and higher efficiency making them a cost-saving option for many new generation and retrofit machines.



Servo Controllers and Software

Perfectly integrated with our Servo Valves, Servo Motors and Servo Drives, as well as hydraulic products, Moog Controllers help support an integrated system approach that provides benefits beyond what individual, off-the-shelf components can offer. From Motion Controllers to Machine Controllers to specialized controllers such as our Test Controllers, we offer hardware and software that is tailored to the requirements of unique applications, making these intelligent servo controllers the ideal choice of machine designers who want to take their equipment in new directions.



And much more

For example, Moog Radial Piston Pumps, Integrated Hydraulic Manifold Systems and Cartridge Valves uphold our reputation for performance and design modularity. And like our other product lines, these key components are always being redesigned and re-imagined for new and exciting applications.

What's next?

Today, Moog continues to add to, enhance, reconfigure and redesign our product lines to ensure flexibility in cutting-edge applications. Current product and system initiatives include:

- Incorporating greater connectivity
- Adding embedded intelligence and software
- Enhancing total system integration
- Reducing energy consumption
- Improving usability and ease-of-use

Wherever industrial applications may evolve, we'll continue to design and build motion control solutions that not only keep pace with industry—but move it in bold new directions.



GOING WHEREVER YOUR IMAGINATION LEADS

From designing an electric actuator for flight simulators in the US to helping an Italian steel mill significantly improve its gauge control to working with a Japanese plastics machine manufacturer to develop the next generation of injection-molding machinery, Moog motion control solutions impact companies in more than 150 countries in every corner of the world.

Worldwide presence

Our approach is simple and powerful. By having Moog teams living and working in so many different countries, we understand the global nuances of how and why our products are used. Which means we are well versed at designing key solutions for specific markets. And always willing to modify or adapt products to fit your unique applications.

This unsurpassed level of local know-how, regional expertise and design flexibility ensures our motion control solutions are tailored to their environment. We know the machine regulations and performance standards. We understand the types of technical data our customers require. Our plants and facilities are right next door. In short, our entire team, from design engineering to customer service, is attuned to your business on a local level.

Expert services





Our commitment to customer collaboration never ends with the sale. Moog Global Support™ is our promise to offer world-class repair and maintenance services delivered expertly by our trained technicians. We help customers reduce their downtime by keeping critical machines running at peak performance.

In addition to factory repair services using OEM parts, Moog offers stock management of spare parts, onsite services for quicker commissioning, set-up and diagnostics and flexible programs for upgrades, preventative maintenance and multi-year contracts. It all adds up to the assurance that no matter where you work, we're there for you to ensure your motion control applications are well managed and maintained. And we're always ready for what's next.

IT'S TIME TO MOVE AHEAD

World-class solutions. Design flexibility. Global depth and support. All delivered by experts who understand your vision and are committed to helping you achieve it. It's what Moog is all about.

Whatever your next motion control challenge may be, we invite you to meet with us. Together, we can advance your ideas. Overcome your toughest obstacles. Create better ways of working. And move your world to new places.



TAKE A CLOSER LOOK.

Moog solutions are only a click away. Visit our worldwide website for more information and the Moog facility nearest you.

Argentina
+54 11 4326 5916
info.argentina@moog.com

India
+91 80 4057 6605
info.india@moog.com

Singapore
+65 677 36238
info.singapore@moog.com

Australia
+61 3 9561 6044
info.australia@moog.com

Ireland
+353 21 451 9000
info.ireland@moog.com

South Africa
+27 12 653 6768
info.southafrica@moog.com

Brazil
+55 11 3572 0400
info.brazil@moog.com

Italy
+39 0332 421 111
info.italy@moog.com

Spain
+34 902 133 240
info.spain@moog.com

Canada
+1 716 652 2000
info.canada@moog.com

Japan
+81 46 355 3767
info.japan@moog.com

Sweden
+46 31 680 060
info.sweden@moog.com

China
+86 21 2893 1600
info.china@moog.com

Korea
+82 31 764 6711
info.korea@moog.com

Switzerland
+41 71 394 5010
info.switzerland@moog.com

Finland
+358 10 422 1840
info.finland@moog.com

Luxembourg
+352 40 46 401
info.luxembourg@moog.com

United Kingdom
+44 168 429 6600
info.uk@moog.com

France
+33 1 4560 7000
info.france@moog.com

The Netherlands
+31 252 462 000
info.thenetherlands@moog.com

USA
+1 716 652 2000
info.usa@moog.com

Germany
+49 7031 622 0
info.germany@moog.com

Norway
+47 6494 1948
info.norway@moog.com

Hong Kong
+852 2 635 3200
info.hongkong@moog.com

Russia
+7 8 31 713 1811
info.russia@moog.com

www.moog.com/industrial

Moog is a registered trademark of Moog Inc. All trademarks as indicated herein are the property of Moog Inc. and its subsidiaries.
©2011 Moog Inc. All rights reserved.

Capabilities brochure
Mobium/Rev.3, March 2011, Id. CDL7132-en