SERVOVALVES PILOT OPERATED FLOW CONTROL VALVE WITH ANALOG INTERFACE 771 SERIES: ISO 10372-02-02-92 772 SERIES: ISO 10372-03-03-092 773 SERIES: MOOG SPECIFIC

HIGH PERFORMANCE, TWO-STAGE DESIGN PROVIDING FLOW CONTROL IN A SIMPLE AND DEPENDABLE, LONG-LIFE DESIGN



Rev. N, April 2024

WHAT MOVES YOUR WORLD

Whenever the highest levels of motion control performance and design flexibility are required, you'll find Moog expertise at work. Through collaboration, creativity and world-class technological solutions, we help you overcome your toughest engineering obstacles. Enhance your machine's performance. And help take your thinking further than you ever thought possible.

### TABLE OF CONTENTS

INTRODUCTION	
Product Overview	3
Features and Benefits	4
Description of Operation	5
TECHNICAL DATA	
Performance Characteristics	6
Dynamic Characteristics	7
Electrical Data	8
Installation Drawings and Null Adjust Instructions	9
Hole Pattern for Mounting Surface	10
BACKGROUND	
Null Flow Adjustment	12
Flow Calculation and Null Cut Options	13
Related Products	14
Routine Maintenance Guidelines	15
About Moog	16
ORDERING INFORMATION	
Accessories and Spare Parts	18
Ordering Code	19



This catalog is for users with technical knowledge. To ensure all necessary characteristics for function and safety of the system, the user has to check the suitability of the products described herein. The products described herein are subject to change without notice. In case of doubt, please contact Moog.

Moog is a registered trademark of Moog Inc. and its subsidiaries. All trademarks as indicated herein are the property of Moog Inc. and its subsidiaries. For the full disclaimer refer to www.moog.com/literature/disclaimers.

For the most current information, visit www.moog.com/industrial or contact your local Moog office.

### **PRODUCT OVERVIEW**

The 77X Series flow control servo valves are throttle valves for 3 and preferably 4-way applications. They are a high performance, 2-stage design that covers the range of rated flows from 4 to 57 l/min (1 to 15 gpm) at 210 bar (3000 psi) valve pressure drop per spool land.

The output stage of the valve is a closed center, four-way sliding spool. The pilot stage is a symmetrical double-nozzle and flapper, driven by a double air gap, dry torque motor. Mechanical feedback of spool position is provided by a cantilevered spring. The valve design is simple and rugged for dependable, long life operation.

These valves are suitable for electrohydraulic position, speed, pressure or force control systems with high dynamic response requirements. The 77X is ideally suited for applications where superior dynamics are a must.

Intrinsically safe valve versions are available for use in applications with potentially hazardous environments. Specific models are certified to FM, ATEX, CSA, TIIS and IECEx standards.

	771		772		773
Valve design	2-stage, wi	th spool and bus	hing and dry	/ torque motor	
Mounting surface	ISO 10372-	02-02-0-92	ISO 10372	2 -03-03-0-92	Moog Specific
Maximum operating pressure	210 bar (30	100 psi)	· · ·		
Maximum Flow	17 l/min (4.4 gpm)		57 l/min (15.0 gpm)		63 l/min (16.5 gpm)
Pilot stage	Nozzle-flap	per			
Rated flow at ∆ p <sub>n</sub> 35 bar / spool land ( 500 psi /spool land)	4 l/min (1 gpm)	10 l/min ( 2.5 gpm)	19 l/min (5.0 gpm)	38 l/min (10.0 gpm)	57 l/min (15.0 gpm)
Step response time for 0 to 100 % stroke	4 ms	4 ms	4 ms	10 ms	17 ms



Intrinsically safe valve versions are available for use in potentially hazardous environments. Specific models are certified to FM, ATEX, CSA TIIS and IECEx standards. Contact Moog for details.

### FEATURES AND BENEFITS

The 77X Series is proven technology that performs reliably in machines where high performance, stability and accuracy are required. Moog's Mechanical Feedback Valves are designed to provide high reliability and long service life.

Features	Benefits
2-stage design with dry torque motor	Compatibility with many different fluids
Low friction, double nozzle pilot stage	Symmetrical build provides maximum stability over a variety of conditions
High spool control force	Stable consistent flows can be achieved, thus increasing accuracies
High dynamics	Increased production cycles
Rugged, long-life design	Reduced maintenance and down time
High resolution, low hysteresis	Improved accuracies for close tolerance applications
Set up at the factory	Allows easy installation and setup
Intrinsically safe or explosive proof valve versions are environments	Able to be employed in most hazardous environments
Field adjustable null bias	Adjustable for perfect alignment when interchanging equipment
Loss of electrical signal results in a zero position failsafe	Predictable, safe operation

### **DESCRIPTION OF OPERATION**


The 77X Series Flow Control Servo Valve consists of a polarized electrical torque motor and two stages of hydraulic power amplification. The motor armature extends into the air gaps of the magnetic flux circuit and is supported in this position by a flexure tube. The flexure tube acts as a seal between the electromagnetic and hydraulic sections of the valve. The 2 motor coils surround the armature, one on each side of the flexure tube.

The flapper of the first stage hydraulic amplifier is rigidly attached to the midpoint of the armature. The flapper extends through the flexure tube and passes between 2 nozzles, creating two variable orifices between the nozzle tips and the flapper. The pressure controlled by the flapper and nozzle variable orifice is fed to the end areas of the second stage spool. The second stage is a conventional four-way spool design in which output flow from the valve, at a fixed valve pressure drop, is proportional to spool displacement from the null position. A cantilevered feedback spring is fixed to the flapper and engages a slot at the center of the spool. Displacement of the spool defects the feedback spring which creates a force on the armature/flapper assembly.

Input signals induce a magnetic charge in the armature and cause a deflection of the armature and flapper. This assembly pivots about the flexure tube and increases the size of one nozzle orifice and decreases the size of the other.

This action creates a differential pressure from the one end of the spool displacement causing a force in the feedback wire which opposes the original input signal torque. Spool movement continues until the feedback wire force equals the input signal force.





# 77X SERIES SERVO VALVES

#### General Technical Data

Valve design	2-stage, with spool and bushing
Pilot valve	Nozzle Flapper
Mounting surface	<b>771 -</b> ISO 10372-02-02-0-92 <b>772 -</b> ISO 10372-03-03-0-92 <b>773 -</b> Moog specific
Installation position	Any orientation, fixed or movable
Weight	0.86 kg (1.9 lb)
Storage temperature range	-40 to +60 °C (-40 to +140 °F)
Ambient temperature range	-40 to +135 °C (-40 to +275 °F)
Vibration resistance (general)	30 g, 3 axis, 10 Hz to 2 kHz
Shock resistance (general)	30 g, 3 axis
Seal material	Fluorocarbon (FKM) (Viton™ B) 90 shore Others upon request


#### Hydraulic Data


Maximum operating pressure				
Ports P, A and B	210 bar (3,000 psi)			
Port T	210 bar (3,000 psi)			
Rated flow at $\Delta p_N$ 35 bar/spool land (500 psi/spool land)	4/10/19/38/57 l/min (1/2.5/5/10/15 gpm)			
Maximum flow				
771	19 l/min (5 gpm)			
772	38 l/min (10 gpm)			
773	57 l/min (15 gpm)			
Maximum main stage leakage flow rate ( $pprox$ zero lap)	2.3 l/min (0.60 gpm)			
Null adjust authority	Greater than 10% of rated flow			
Hydraulic fluid	Hydraulic oil as per DIN 51524 parts 1 to 3 and ISO 11158 Other fluids on request			
Temperature range	-40 to +135 °C (-40 to +275 °F)			
Recommended viscosity range	10 to 97 mm²/s (cSt) @ 38 °C			
Maximum permissible viscosity range	5 to 1,250 mm²/s (cSt) @ 38 °C			
Recommended filter rating				
For functional safety	β <sub>10</sub> 75 (10 μm absolute)			
For longer life	ß <sub>5</sub> 75 (5 μm absolute)			

#### Static and Dynamic Data


Rated flow	4 l/min (1 gpm)	10 l/min (2.5 gpm)	19 l/min (5 gpm)	38 l/min (10 gpm)	57 l/min (15 gpm)	
Deviation of rated flow	± 10% of rated flow					
Step response time 0-100% stroke	4 ms	4 ms	4 ms	10 ms	17 ms	
Threshold	$\leq$ 0.5% of rated	≤0.5% of rated signal				
Hysteresis	≤3.0% of rated signal					
Null shift for △T - 38°C (100°F)	≤2.0% of rated signal					

### 77X SERIES SERVO VALVES -STANDARD RESPONSE SERVO VALVES






4, 10 and 19 l/min (1, 2.5 and 5 gpm) Plot 1 & 3 = ±40% rated signal (solid) Plot 2 & 4 = ±100% rated signal (dash)



38 l/min (10 gpm)Plot 1 & 3 = ±40% rated signal (solid) Plot 2 & 4 = ±100% rated signal (dash)



Plot 2 & 4 =  $\pm 100\%$  rated signal (solid)

### **ELECTRICAL DATA**

#### Rated current and coil resistance

A variety of coils are available for 77X Series Servo Valves, which offer a wide choice of rated currents.

#### Coil impedance

The resistance and inductance of standard coils are given below. The 2 coils in each Servo Valve are wound with equal turns giving a normal production tolerance on coil resistance of  $\pm 12$  %. Copper magnet wire is used, so the coil resistance will vary significantly with temperature. The effects of coil resistance changes can be essentially eliminated through use of a current feedback servoamplifier having high output impedance.

Inductance is determined under pressurized operating conditions and is greatly influenced by back electromagnetic forces of the torque motor. These effects vary with most operating conditions, and vary greatly with signal frequencies above 100 Hz. The apparent coil inductance values given are determined at 50 Hz.


Ordering Code	Comman	d signal (r	nA)	Coil resistance [Ohms/coil at	Power co	nsumptio	n [W]	Coil indu sured at	ctance [H] 50 Hz	mea-
	Single coil	Series coil	Parallel coil	25 °C (77 °F)]	Single coil	Series coil	Parallel coil	Single coil	Series coil	Parallel coil
н	±15	±7.5	±15	206	0.046	0.0	)23	0.72	2.2	0.59
L	±40	±20	±40	80	0.128	0.0	)64	0.22	0.66	0.18

#### Coil connections


A 4-pin electrical connector that mates with an MS3106F14S-2S is standard. All 4 torque motor leads are available at the connector so that external connections can be made for series, parallel, or differential operation. 77X Series Servo Valves can be supplied on special order with other connectors or pigtail.

#### Configuration for valve opening $P \longrightarrow B$ , $A \longrightarrow T$

#### Single




Series




A (+), D (-), B and C connected

Parallel



### INSTALLATION DRAWINGS AND NULL ADJUST INSTRUCTIONS



- 1 Typical wiring schematic
- **2** Location pin (refer to section Hole Pattern for position)
- 3 Valve mounting holes: 4X Ø 5.61 mm (0.221 in) or Ø 6.73 mm (0.265 in) thru
- 4 Null adjust screw (requires 3/8" wrench and 3/32" hex key)
- **5** Connector mates with MS3106F14S-2S

#### Notes:

#### Fluid:

Industrial hydraulic fluid per DIN 51524 parts 1 to 3 and ISO 11158, maintained to ISO 4406 Code 17/14/11 recommended Viscosity 10 to 97 mm<sup>2</sup>/s (cSt) at 38 °C (60 to 450 SUS at 100 °F)

#### **Operating Temperature Range:**

Fluid: -40 to +60 °C (-40 to +140 °F) Ambient: -40 to +135 °C (-40 to +275 °F)

#### Valve Phasing:

Flow out port B results when: Series coils: B & C connected, A+, D-Parallel coils: A & C connected, B & D connected, A and C+, B and D-Single coils: A+/B- or C+/D-


#### Surface:

Surface to which valve is mounted requires flatness of 0.05 mm (0.002 in) over 100 mm (3.94 in) and an average finish  $R_{\rm a}$  better the 0.8  $\mu m$  (0.000032 in)

#### Null Adjust:

Flow out port B results with the clockwise rotation of the null adjust screw

# 77X SERIES HOLE PATTERN FOR MOUNTING SURFACE



771 Designation		Р	A	В	Т	G	F1	F2	F3	F4
Size Ø	mm	4.85	4.85	4.85	4.85	3.45	M5	M5	M5	M5
	in	0.191	0.191	0.191	0.191	0.136	.190-32	.190-32	.190-32	.190-32
Position X	mm	21.44	13.50	29.38	21.44	11.53	0	42.88	42.88	0
	in	0.844	0.532	1.157	0.844	0.454	0	1.688	1.688	0
Position Y	mm	9.13	17.07	17.07	25.01	4.37	0	0	34.14	34.14
	in	0.360	0.672	0.672	0.985	0.172	0	0	1.344	1.344
772 Designation		Р	Α	В	Т	G	F1	F2	F3	F4
Size Ø	mm	6.63	6.63	6.63	6.63	3.45	M5	M5	M5	M5
	in	0.261	0.261	0.261	0.261	0.136	.190-32	.190-32	.190-32	.190-32
Position X	mm	21.44	11.53	31.34	21.44	11.53	0	42.88	42.88	0
	in	0.844	0.454	1.234	0.844	0.454	0	1.688	1.688	0
Position Y	mm	7.16	17.07	17.07	26.97	4.37	0	0	34.14	34.14
	in	0.282	0.672	0.672	1.062	0.172	0	0	1.344	1.344
773 Designation	1	Р	A	В	Т	G	F1	F2	F3	F4
Size Ø	mm	7.92	7.92	7.92	7.92	3.45	M6	M6	M6	M6
	in	0.312	0.312	0.312	0.312	0.136	.250-20	.250-20	.250-20	.250-20
Position X	mm	21.44	9.54	33.34	21.44	11.53	0	42.88	42.88	0
	in	0.844	0.376	1.313	0.844	0.454	0	1.688	1.688	0
Position Y	mm	5.17	17.07	17.07	28.97	4.37	0	0	34.14	34.14
	in	0.204	0.672	0.672	1.141	0.172	0	0	1.344	1.344

## 77X SERIES HOLE PATTERN FOR MOUNTING SURFACE

### Ports

For maximum flow ports must be designed as follows:

- 771: 4.85 mm (0.191 in) diameter, counter-bored 9.52 mm (0.375 in) by 1.40 mm (0.055 in) deep
- 772: 6.60 mm (0.260 in) diameter, counter-bored 12.65 mm (0.498 in) by 1.40 mm (0.055 in) deep
- 773: 7.92 mm (0.312 in) diameter, counter-bored 14.27 mm (0.562 in) by 1.40 mm (0.055 in) deep

### **Recommended Mounting Seals**

Material dependent on application

- 771: 1.78 mm (0.070 in) cross section x 6.07 mm (0.239 in) inside diameter, 90 durometer. Equivalent AS83248/2 size -010
- 772: 1.78 mm (0.070 in) cross section x 9.24 mm (0.364 in) inside diameter, 90 durometer. Equivalent AS83248/2 size -012
- 773: 1.78 mm (0.070 in) cross section x 10.82 mm (0.426 in) inside diameter, 90 durometer. Equivalent AS83248/2 size -013

#### **Reccomended Mounting Screws**

Material dependent on application


- 771: SHCS 0.190 x 2.0 long. Grade 8 minimum
- 771: SHCS M5 x 50 long. Grade 10.9 minimum
- 772: SHCS 0.190 x 2.0 long. Grade 8 minimum
- 772: SHCS M5 x 50 long. Grade 10.9 minimum
- 773: SHCS 0.250 x 2.25 long. Grade 8 minimum
- 773: SHCS M6 x 60 long. Grade 10.9 minimum

### NULL FLOW ADJUSTMENT

It is often desirable to adjust the null flow of a servo valve independently of other system parameters. Valves with mechanical null adjustment allow for at least ±10% adjustment of null flow. The mechanical null adjustment is an eccentric bushing retainer pin, located above the tank port designation on the valve body, which if rotated provides control of the bushing location. Mechanical feedback elements position the spool relative to the valve body for a given input signal. Therefore, a movement of the bushing relative to the body changes the null flow.

#### Mechanical Adjustment Procedure

With zero current (electrical connector disconnected). Using a 3/8 inch offset wrench, loosen the self-locking fitting until the null adjustor pin can be rotated. (This should usually be less than 1/2 turn). DO NOT remove the self-locking fitting. Insert a 3/32 inch Allen wrench in the null adjustor pin. Use the 3/32 Allen wrench to rotate the mechanical adjustor pin to obtain the desired null flow. Re-torque the self-locking fitting to 57 in lbs.




### **FLOW CALCULATION**

The actual flow is dependent upon the electrical command signal and valve pressure drop. The flow for a given valve pressure drop can be calculated using the square root function for sharp edge orifices.

$$Q = Q_N \sqrt{\frac{\Delta p}{\Delta p_N}}$$


Q	actual flow
Q <sub>N</sub>	rated flow
Δp	actual pressure drop per spool land
$\Delta p_{\rm N}$	rated pressure drop per spool land

#### Flow Diagram




### SPOOL NULL CUT OPTIONS

#### **Standard Axis Cut**




Default, without request for optional cuts

#### **Open Center Spool Valves**



Normally used in hydraulic motor applications

**Closed Center Spool Valves** 



Normally used in failsafe applications

### **RELATED PRODUCTS**

#### Din Rail Modules - Analog Control Cards

Moog's DIN rail mounted module analog control cards are ideal for use in enclosures where space is limited. Modules include servoamplifers, transducer conditioning electronics, command and auxiliary function modules, valve drive amplifiers, and power supplies. All of these modules are CE marked and require a 24V DC supply. The modules mount to standard 35mm DIN rail mount for easy installation and removal.

#### Portable Valve Testers - Evaluates Valves in the Field

Valve testers are a cost effective method for evaluating valves in the field. They provide a quick and easy means of differentiating between hydraulic and electronic problems. There are five models to choose from, each with different levels of capability and flexibility to meet your specific requirements. All valve testers have a compact, easily portable design.

# Filtration - Oil Filtration Requirements for Industrial Servo Systems


The most effective way to reduce life cycle costs of an oil hydraulic system, regardless of the types of valve used, is through close attention to contamination control. For industrial servo systems the ideal system filter arrangement is summarized as follows:

- Use a 10 micron (Beta 10 >= 75) high pressure filter without by-pass just before the valve or critical parts of the valve (e.g. pilot)
- Use a 3 micron (Beta 3 >= 75) low pressure filter in the return or bypass line.
- Use a filter in the tank breather that is at least the same filtration level as the finest filter in the system.

This recommendation is based on the fact that most servo and proportional valves can accept the odd particle up to 25 microns so the pressure filter will protect the valve from catastrophic failure. The real work is done by the low pressure filter reducing the small particle contamination which is the prime contributor to component wear and silting.

Assuming that the filters are properly dimensioned and care is taken during initial installation and maintenance, the aim should be to limit oil contamination to 16/13 (under ISO 4406:1987) or 17/14/11 (under ISO 4406: 1999).

For long life, the maximum levels per ISO 4406: 1987 and 1999 are 13/10 and 16/13/10, respectively. It is important to note that these are maximum contamination levels and with proper care and regular filter change, significantly lower levels can and should be achieved. Attention must also be paid to a number of other factors that contribute to oil condition problems such as elevated temperatures, high tank humidity, "dirty" new oil, etc.



**Din Rail Module** 



Valve Tester



**Hydraulic Filters** 

### **ROUTINE MAINTENANCE GUIDELINES**

Every six months or 4,000 operating hours, check for proper operation of the control valve assembly by performing the preventative maintenance steps outlined below. These checks do not require removal of the valve from the process line. If a problem is suspected, repair the valve assembly prior to returning the unit to service.

- Replace the hydraulic filter element
- Stroke the valve and check for smooth, full-stroke operation; unsteady motion could indicate a servo valve, actuator or process valve problem

#### **GENERAL INFORMATION**

#### **Effects when Storing Valves**

The following effects may occur when storing valves for a long time:

- Sealing materials become brittle, possibly resulting in leaks
- Hydraulic fluid becomes gummy, possibly resulting in friction
- Electrolytic capacitors of the valve electronics may fatigue, possibly resulting in adverse effects on the valve electronics

#### Storage Time

The storage time starts at stock receipt and ends at mounting of the valve.

#### Preservatives

If conservation is carried out, use only conservatives which are compatible with the sealing materials and do not affect the valve, spare parts and accessories.

#### **BEFORE STORAGE**

**Note:** If the valves are exposed to aggressive environmental influences during storage, vacuum packaging may be necessary. We recommend the following preparatory measures for storage:

#### Mount the shipping plate on the valve.

This is the only way of adequately protecting the valves against the ingress of dirt and moisture and protecting the seals against the effects of ozone and UV.

#### Put the valve, spare parts and accessories into the original packaging.

Package each valve separately.

# Enclose anti-tarnish paper or package the valve, spare parts and accessories with corrosion inhibiting film.

(Only for storage time > 1 year.)

Multipacks of single valves in their individual packages are allowed.

#### Seal the original packaging properly.

This is the only way of adequately protecting the valves, spare parts and accessories against damage.

#### **STORAGE CONDITIONS**

We recommend the following ambient conditions for storage:

- Dust-free, moderately ventilated
- As vibration-free and shock-free as possible

Shock resistance (as per EN 60068-2-27): 50 g, 6 directions, half-sine 3 ms

Vibration resistance (as per EN 60068-2-6): 30 g, 3 axes, frequency 10 to 2,000 Hz

#### Temperature

Recommended: +15 to +25 °C (+59 to +77 °F)

Permissible: -40 to +60 °C (-40 to +140 °F)

Temperature fluctuations >10 °C (50 °F) must be avoided.

Distance to shielded radiators: > 1 m (3 ft)

No direct exposure to sunlight

No sources of light with a high UV content

UV rays generate ozone, which damage sealing materials.

Relative air humidity: < 65 %, non condensing

#### AFTER STORAGE

We recommend to check the original packaging, valve, spare parts and accessories for possible damage or alterations due to storage, that is, before use.

Damaged or not functional valves, spare parts and accessories must not be started up.

Sealing materials with the following characteristics must not be used:

- Contamination
- Cracking
- Hardening/softening
- Stickiness
- Discoloration

#### Storage Time > 5 Years

We recommend that the valve be checked by us or one of our authorized service centers after a storage time of more than 5 years.

#### Storage Time > 10 Years

After a storage time of more than 10 years the valves have to be checked by us or one of our authorized service centers.

### **ABOUT MOOG**

Moog Inc. is a worldwide designer, manufacturer and integrator of precision control components and systems. Moog's Industrial Group designs and manufactures high performance motion control solutions combining electric, hydraulic, and hybrid technologies with expert consultative support in a range of applications including energy production and generation machinery, industrial production machinery and simulation and test equipment. We help performance-driven companies design and develop their next-generation machines.

Moog maintains facilities in 26 countries around the globe. This vast scope ensures that our engineers remain close to the needs of machine builders and provide flexible design solutions and technical expertise tailored to our customers' toughest challenges.

Moog experts work in close collaboration with machine builders and application engineers to design motion control systems for greater productivity, higher reliability, superior connectivity, less costly maintenance and more effective operations. Our regional presence, industry knowledge and design flexibility ensures Moog motion control solutions are tailored to their environment from meeting operating regulations and performance standards, to taking machine performance to a higher level.

### Products

At the heart of every Moog solution is an array of products engineered for precision, high performance and reliability. For more than six decades, Moog products have been specified for critical machine applications.

Some are developed specifically for unique operating environments. Others are standard equipment on machines across many industries. All are continuously improved to take advantage of the latest technology breakthroughs and advancements.

Moog products include:

- Servo Valves and Proportional Valves
- Servo Motors and Servo Drives
- Servo Controllers and Software
- Radial Piston Pumps
- Actuators
- Integrated Hydraulic Manifold Systems and Cartridge Valves
- Slip Rings
- Motion Bases



Servo Valves



Active Cartridge Valves



Radial Piston Pumps



Servo Drives

### **ABOUT MOOG**

#### Hydraulic solutions

Since Bill Moog invented the first commercially viable servo valve in 1951, Moog has set the standard for world-class hydraulic technology. Today, Moog products are used in a variety of applications providing high power, enhanced productivity and ever better performance for some of the world's most demanding applications.

#### **Electric solutions**

Clean operation, low noise generation, less maintenance and reduced power consumption make Moog electric solutions ideal for applications worldwide. Moog is the ideal partner for applications where transitioning technologies requires special expertise.

#### Hybrid solutions

By incorporating the advantages of existing hydraulic and electric technologies - including modular flexibility, increased efficiency and cleanliness into innovative hybrid solutions, Moog offers new performance potential in specialized applications.

### **Moog Global Support**

Moog Global Support is our promise to offer world-class Repair and Maintenance Services delivered expertly by our trained technicians. With the reliability only available from a leading manufacturer with facilities around the world, Moog offers you service and expertise you can count on to keep your equipment operating as it should.

This promise offers many benefits to our customers including:

- Reduce your downtime by keeping critical machines running in peak performance
- Protect your investment by ensuring reliability, versatility and long-life of products
- Better plan your maintenance activities and make systematic upgrades
- Leverage our flexible programs to meet the unique service requirements of your facility

Look to Moog for global support including:

- Repair services using OEM parts are performed by trained technicians to the latest specifications
- Stock management of spare parts and products to prevent unplanned downtime



**Flight Simulation** 



Formula One Simulation Table

- Flexible programs, tailored to your needs such as upgrades, preventative maintenance and annual/ multi-year contracts
- On-site services bring the expertise to you, providing quicker commissioning, set-up and diagnostics
- Access to reliable services that are guaranteed to offer consistent quality anywhere in the world

For more information on Moog Global Support visit www.moog.com/industrial/service.




# ACCESSORIES AND SPARE PARTS

Part Name	Description	Material	Moog Part Number
Maintenance kit	Base o-rings	FKM per	B52555RK054K001
	Additional o-rings required for filter access	AMS7259 Note that o-ring material is dependent on application.	
	Filter tube		

#### Documents (not included in scope of delivery)

Part designation	Description	Remark	Moog part number
Catalog	77X series general information	To download document <u>click here</u> or scan below:	CDL6651
Service manual	77X standard series		CDS6674
Service manual	77XK intrinsically safe (K) series		CDS6768

### **ORDERING CODE**



#### Preferred Models

Model Number	Type Designation	Rated Flow (∆1,000 psi) I/min gpm		Rated Current (single or parallel coil) mA
G771-3001A	H04F0FM4VBL	4	1.0	±40
G771-3002A	H10F0FM4VBL	10	2.5	±40
G772-3003A	H19F0FM4VBL	19	5.0	±40
G772-3004A	S38F0FM4VBL	38	10.0	±40
G773-3005A	S57F0GM4VBL	57	15.0	±40

All combinations may not be available. Other options available upon request. Please contact Moog for non-standard configurations.

# MORE PRODUCTS. MORE SUPPORT.

Moog designs a range of motion control products to complement those featured in this document. Moog also provides service and support for all of our products. For more information, contact the Moog facility closest to you.

Australia +61 3 9561 6044 Service + 61 3 8545 2140 info.australia@moog.com service.australia@moog.com

Brazil +55 11 3572 0400 info.brazil@moog.com service.brazil@moog.com

Canada +1 716 652 2000 info.canada@moog.com

China +86 512 5350 3600 info.china@moog.com service.china@moog.com

France +331 4560 7000 Service +331 4560 7015 info.france@moog.com service.france@moog.com

Germany +4970316220 Service +497031622197 info.germany@moog.com service.germany@moog.com

Hong Kong +852 2 635 3200 info.hongkong@moog.com India +91 80 4057 6666 Service +91 80 4057 6604 info.india@moog.com service.india@moog.com

Ireland +353 21 451 9000 info.ireland@moog.com

Italy +39 0332 421 111 Service 800 815 692 info.italy@moog.com service.italy@moog.com

Japan +81 46 355 3767 info.japan@moog.com service.japan@moog.com

Korea +82 31 764 6711 info.korea@moog.com service.korea@moog.com

Luxembourg +352 40 46 401 info.luxembourg@moog.com

The Netherlands +31 252 462 000 info.thenetherlands@moog.com service.netherlands@moog.com Singapore +65 677 36238 Service +65 651 37889 info.singapore@moog.com service.singapore@moog.com

Spain +34 902 133 240 info.spain@moog.com

Sweden +46 31 680 060 info.sweden@moog.com

Turkey +90 216 663 6020 info.turkey@moog.com

United Kingdom +44 (0) 1684 858000 Service +44 (0) 1684 278369 info.uk@moog.com service.uk@moog.com

USA +17166522000 info.usa@moog.com service.usa@moog.com

For product information, visit www.moog.com/industrial

Moog is a registered trademark of Moog Inc. and its subsidiaries. All trademarks as indicated herein are the property of Moog Inc. and its subsidiaries. ©2024 Moog Inc. All rights reserved. All changes are reserved.

77X Series Flow Control Servo Valves STS, Rev. N, April 2024, CDL6651

MOOG | Shaping the way our world moves<sup>™</sup>