

Rev. P, March 2024

HIGH PERFORMANCE, TWO-STAGE DESIGN PROVIDING FLOW CONTROL IN A SIMPLE, RUGGED, DEPENDABLE, LONGLIFE DESIGN



Whenever the highest levels of motion control performance and design flexibility are required, you'll find Moog expertise at work. Through collaboration, creativity and world-class technological solutions, we help you overcome your toughest engineering obstacles, enhance your machine's performance, and help take your thinking further than you ever thought possible.

INTRODUCTION	2
Product Overview	3
Features and Benefits	4
Description of Operation	5
TECHNICAL DATA	6
78 Series - Standard Response Version	6
78 Series - High Response Version	8
Installation Drawing	10
Mounting Requirements	11
Electrical Connection	12
BACKGROUND	13
Flow Calculation	13
Null Cut Options	13
Related Products	14
About Moog	15
ORDERING INFORMATION	17
Accessories and Spare Parts	17
Ordering Code	18

This catalog is for users with technical knowledge. To ensure all necessary characteristics for function and safety of the system, the user has to check the suitability of the products described herein. The products described in this document are subject to change without notice. In case of doubt, please contact Moog.

Moog is a registered trademark of Moog Inc. and its subsidiaries. All trademarks as indicated herein are the property of Moog Inc. and its subsidiaries. For the full disclaimer refer to www.moog.com/literature/disclaimers.

For the most current information, visit www.moog.com/industrial or contact your local Moog office.

PRODUCT OVERVIEW

The 78 series is part of the Moog family of Mechanical Feedback (MFB) Servo Valves. They are throttle valves for 3 and 4 way applications. This series has a high performance, two-stage design that covers a range of rated flows from 75 to 150 l/min (20 to 40 gpm) at 35 bar (500 psi) valve drop per spool land. These valves are intended for position, speed, pressure or force control applications that require high dynamic response. The 78 series MFB offers high dynamics, high resolution and low hysteresis due to its low friction double nozzle pilot stage.

The design is simple and rugged for dependable, long life operation. The output stage is a closed center, 4 way sliding spool. The pilot stage is comprised of a symmetrical, double nozzle dry torque motor. The $2^{\rm nd}$ stage spool position is controlled by a carbide tipped feedback wire. The carbide ball on the end of the feedback wire is a mandatory design requirement that ensures high accuracy, reliable operation and long service life. All of our servo valves are known for high accuracy and reliable operation even in the harshest industrial applications.

This family of valves is considered a flow control servo valve with an analog interface, but does not contain integrated electronics. The options in this series include standard and high response, special null (spool) cuts, seal materials and connectors. Intrinsically safe and flameproof designs for use in hazardous environments are also available with specific models certified to FM, ATEX, CSA and TIIS (Asian) standards.

All of our valves are backed by Moog Global Support, our promise to provide world-class repair and maintenance services delivered by our trained technicians. Each valve possesses a long life design, controlled by proven servo valve technology that has an outstanding history of 60 years of meeting the motion control needs of our customers. All of this makes Moog servo valves the best choice for your hydraulic motion control requirements.

	Standard res		High response valves with Ø 0.406 spool		
Valve design	2-stage, with	spool and bus	hing and dry to	orque motor	
Mounting pattern	Unique to 78 Series				
Maximum operating pressure to ports P, T, A, B	B 210 bar (3000 psi)				
Maximum flow	208 l/min (54	1.9 gpm)		156 l/min (41	2 gpm)
Pilot stage	Nozzle Flapp	er			
Rated flow at ∆p _N 35 bar/spool land (500 psi/spool land)	75 l/min 115 l/min 150 l/min 75 l/min (20 gpm) (40 gpm) (20 gpm)				115 l/min (30 gpm)
Step response time for 0 to 100 % stroke	30 ms 40 ms 15 ms 20 ms				20 ms

















Intrinsically safe and explosion proof valve versions are available for use in potentially hazardous environments. Specific models are certified to FM, ATEX, CSA, TIIS and IECEx standards. Contact Moog for details.

PRODUCT OVERVIEW

Documents

Name	Description	Remark	Number
Catalog	78 series	To download document	CDL6272
Manual	78 standard series	click here or scan below:	CDS6569
	78 intrinsically safe (K) series		CDS6752
	78 explosion proof (N) series	3220	CDS6857
Installation drawing	78 standard series		CC44555
	78 instrinsically safe (K) series		
	78 explosion proof (N) series		CC42165

FEATURES AND BENEFITS

The 78 Series is proven technology that performs reliably in machines where high performance, stability and accuracy are required. Moog's Mechanical Feedback Valves are designed to provide high reliability and long service life. The current technology reflects over 60 years of experience of servo control in some of the world's most demanding environments.

Features	Benefits
100% factory tested to ensure critical specification performance	Ensures smooth and easy startup, reduces downtime and insures long life in critical industrial applications
2 Stage Design	Enables high machine performance, faster cycle times and greater accuracy - all resulting in higher productivity
Dual Coil torque motor	Redundancy for high reliability
Dual Precision Nozzles in Torque Motor	Precision flow control and predictability
Dry torque motor design	Eliminates potential contamination issues in the air gaps of the torque motor that could cause machine downtime
Hardened 440C Bushing and Spool	Provides for high life, wear resistance when used in the harsh environments; provides for low sliding friction during use
Emergency failsafe positioning	Most valves are set up to return to a failsafe position when the command signal is interrupted or eliminated
Field replaceable pilot stage filter	Enables preventive maintenance in the field, saving precious machine downtime and service costs
External null bias adjustment	Enables technicians to manually adjust the null bias of the valve to adapt to the conditions of the machine. This feature provides a simple adjustment to machine performance without the need to adjust a controller.

DESCRIPTION OF OPERATION


The 78 Series Flow Control Servo Valve consists of a polarized electrical torque motor and two stages of hydraulic power amplification. The torque motor armature extends into the air gaps of the magnetic flux circuit and is supported in this position by a flexure tube. The flexure tube acts as a seal between the electromagnetic and hydraulic sections of the valve. The 2 torque motor coils surround the armature, one on each side of the flexure tube.

The flapper of the first stage hydraulic amplifier is rigidly attached to the midpoint of the armature. The flapper extends through the flexure tube and passes between 2 nozzles, creating two variable orifices between the nozzle tips and the flapper. The pilot pressure is controlled by the flapper/nozzle variable orifice and is in turn fed to the end areas of the second stage spool. This action creates a differential pressure from one end of the spool to the other and results in spool displacement. The spool displacement causes a force in the feedback wire which opposes the original input signal torque. Spool movement continues until the feedback wire force equals the input signal force.

The second stage is a conventional four-way spool design in which output flow from the valve, at a fixed valve pressure drop, is proportional to spool displacement from the null position. A cantilever feedback spring is fixed to the flapper and engages a slot at the center of the spool. Displacement of the spool deflects the feedback spring which creates a force on the armature/flapper assembly.

Input signal induces a magnetic charge in the armature and causes a deflection of the armature and flapper. This assembly pivots about the flexure tube and increases the size of one nozzle orifice and decreases the size of the other.

Electro-hydraulic Servo Valve Cut-away



78 SERIES - STANDARD RESPONSE VERSION

General Technical Data

Valve design	2-stage, with spool and bushing and dry torque motor
Pilot stage	Nozzle Flapper
Mounting pattern	Unique to 78 Series
Installation position	Any orientation, fixed or movable
Weight	2.86 kg (6.3 lb)
Storage temperature range	-40 to +60 °C (-40 to +140 °F)
Ambient temperature range	-40 to +135 °C (-40 to +275 °F)
Vibration resistance	30 g, 3 axis, 10 Hz to 2 kHz
Shock resistance	30 g, 3 axis
Seal material	Fluorocarbon (FKM) 85 Shore D Others upon request


Hydraulic Data

Maximum operating pressure to ports P, T, A, B	210 bar (3,000 psi)					
Rated flow at Δp_N 35 bar/spool land (500 psi/spool land)	75 l/min (20 gpm)	115 l/min (30 gpm)	150 l/min (40 gpm)			
Maximum flow	208 l/min (54.9 gpr	n)				
Null adjust authority	Greater than 10 %	of rated flow				
Hydraulic fluid	Hydraulic oil as per DIN 51524 parts 1 to 3 and ISO 11158 Other fluids on request.					
Temperature range	-40 to +60 °C (-40 to +140 °F)					
Recommended viscosity range	10 to 85 mm ² /s (cS	t)				
Maximum permissible viscosity range	5 to 1250 mm ² /s (c	St)				
Recommended cleanliness class as per ISO 4406						
For functional safety	17/14/11					
For longer service life	15/13/10					
Recommended filter rating						
For functional safety	$\beta_{10} = 75 (10 \mu \text{m absolute})$					
For longer life	$\beta_s = 75 (5 \mu\text{m absolute})$					

Static and Dynamic Data


Sample deviation of rated flow	±10 %		
Step response time for 0 to 100 % stroke	30 ms	30 ms	40 ms
Threshold	0.5 %		
Hysteresis	< 3.0 %		
Null shift at $\Delta T = 38 ^{\circ}\text{C} (100 ^{\circ}\text{F})$	< 2.0 %		

78 SERIES - STANDARD RESPONSE VERSION




Reduced Amplitude Step Response

33 % step Plot 1 = 75/115 l/min (20/30 gpm) Plot 2 = 150 l/min (40 gpm)




Full Amplitude Step Response

100 % step Plot 1 = 75/115 l/min (20/30 gpm)Plot 2 = 150 l/min (40 gpm)



Standard Frequency Response

75/115 l/min (20/30 gpm) Plot $1 \& 3 = \pm 40 \%$ rated signal Plot $2 \& 4 = \pm 100 \%$ rated signal



Standard Frequency Response

154 l/min (40 gpm)
Plot 1 & 3 = ±40 % rated signal
Plot 2 & 4 = ±100 % rated signal

Note: Measured with 210 bar (3,000 psi), DTE $^{\circ}$ -24 fluid at +38 $^{\circ}$ C (+100 $^{\circ}$ F)

78 SERIES - HIGH RESPONSE VERSION

General Technical Data

Valve design	2-stage, with spool and bushing and dry torque motor
Pilot stage	Nozzle Flapper
Mounting pattern	Unique to 78 Series
Installation position	Any orientation, fixed or movable
Weight	2.86 kg (6.3 lb)
Storage temperature range	-40 to +60 °C (-40 to +140 °F)
Ambient temperature range	-40 to +135 °C (-40 to +275 °F)
Vibration resistance	30 g, 3 axis, 10 Hz to 2 kHz
Shock resistance	30 g, 3 axis
Seal material	Fluorocarbon (FKM) 85 Shore D Others upon request


Hydraulic Data

Maximum operating pressure to ports P, T, A, B 210 bar (3,000 psi)					
Rated flow at Δp_N 35 bar/spool land (500 psi/spool land)	75 l/min (20 gpm)	115 I/min (30 gpm)			
Maximum flow	156 l/min (41.2 gpm)				
Null adjust authority	Greater than 10 % of rated flo	W			
Hydraulic fluid Hydraulic oil as per DIN 51524 parts 1 to 3 and ISO Other fluids on request.					
Temperature range	-40 to +60 °C (-40 to +140 °F)				
Recommended viscosity range	10 to 85 mm ² /s (cSt)				
Maximum permissible viscosity range	5 to 1250 mm ² /s (cSt)				
Recommended cleanliness class as per ISO 4406					
For functional safety	17/14/11				
For longer service life	15/13/10				
Recommended filter rating					
For functional safety	$\beta_{10} = 75 (10 \mu \text{m absolute})$				
For longer life	β_{5} = 75 (5 µm absolute)				

Static and Dynamic Data


Sample deviation of rated flow	±10 %	
Step response time for 0 to 100 % stroke	15 ms	20 ms
Threshold	0.5 %	
Hysteresis	< 3.0 %	
Null shift at $\Delta T = 38 ^{\circ}\text{C} (100 ^{\circ}\text{F})$	< 2.0 %	

78 SERIES - HIGH RESPONSE VERSION




Reduced Amplitude Step Response

33 % step Plot 1 = 75 l/min (20 gpm) Plot 2 = 115 l/min (30 gpm)




Full Amplitude Step Response

100 % step Plot 1 = 75 l/min (20 gpm) Plot 2 = 115 l/min (30 gpm)



High Frequency Response

75 I/min (20 gpm) Plot $1 \& 3 = \pm 40 \%$ rated signal Plot $2 \& 4 = \pm 100 \%$ rated signal




High Frequency Response

115 l/min (30 gpm) Plot $1 \& 3 = \pm 40 \%$ rated signal Plot $2 \& 4 = \pm 100 \%$ rated signal

Note: Measured with 210 bar (3,000 psi), DTE $^{\circ}$ -24 fluid at +38 °C (+100 °F)

INSTALLATION DRAWING




Note: Dimensions in mm (in)

- 1 Locating pin
- 2 Filter and plug location
- 3 Mechanical null adjust
- 4 Optional magnetic null adjust

- 5 Electrical connector (as shown, mates with MS3106F14S-2S)
- 6 Filter
- 7 Filter plug

MOUNTING REQUIREMENTS



Designation		Ports				Locating Pin	g Mounting Holes			
		Р	Α	В	Т	G	F1	F2	F3	F4
Size Ø	mm in	15.88 0.625	15.88 0.625	15.88 0.625	15.88 0.625	3.96 0.156	M8 5/16-18	M8 5/16-18	M8 5/16-18	M8 5/16-18
Position X	mm in	46.02 1.812	68.25 2.687	23.80 0.937	46.02 1.812	66.65 2.624	0	92.08 3.625	92.08 3.625	0
Position Y	mm in	52.37 2.062	30.15 1.187	30.15 1.187	7.92 0.312	50.77 1.999	0	0	60.33 2.375	60.33 2.375

Surface

Surface to which the valve is mounted requires:

- Flatness of 0.01 mm (0.004 in) over 100 mm (3.94 in)
- Average finish R_a better than 0.8 µm (0.000032 in)

Ports

For maximum flow the ports must be designed as follows:

• P, T, A, and B must be designed with diameters of 16 mm (0.625 in)

Recommended Mounting Seals

- Material dependent on application
- 1.78 mm (0.070 in) cross section x 18.77 mm (0.739 in) inside diameter. 90 durometer
- Equivalent AS83248/2 size -018

Recommended Mounting Screws

- Material dependent on application
- SHCS 5/16 x 3.0 long. Grade 8 minimum
 SHCS M8 x 75 long. Grade 10.9 minimum

ELECTRICAL CONNECTION

Rated Current and Coil Resistance

A variety of coils are available for 78 Series Servo Valves, which offer a wide choice of rated currents.

Coil Impedance

The resistance and inductance of standard coils are given below. The 2 coils in each Servo Valve are wound with equal turns giving a normal production tolerance on coil resistance of ± 12 %. Copper magnet wire is used, so the coil resistance will vary significantly with temperature. The effects of coil resistance changes can be essentially eliminated through use of a current feedback servoamplifier having high output impedance.


Inductance is determined under pressurized operating conditions and is greatly influenced by back electromagnetic forces of the torque motor. These effects vary with most operating conditions, and vary greatly with signal frequencies above 100 Hz. The apparent coil inductance values given are determined at 50 Hz.


Ordering code	Command signal [mA]			Coil resistance [Ohms/coil	Power co	onsumption	n [W]	Coil indu measure	_	- 1
	Single coil	Series coil	Parallel coil	at 25 °C (77 °F)]	Single coil	Series coil	Parallel coil	Single coil	Series coil	Parallel coil
L	±40	±20	±40	80	0.128	0.064		0.22	0.66	0.18
М	±50	±25	±50	80	0.20	0.10		0.22	0.66	0.18
Z	±200	±100	±200	22	0.88	0.4	14	0.07	0.21	0.06


Coil Connections

A 4-pin electrical connector that mates with an MS3106F14S-2S is standard. All 4 torque motor leads are available at the connector so that external connections can be made for series, parallel, or differential operation.


Connection for valve opening $P \rightarrow B$, $A \rightarrow T$







A (+), D (-), B and C connected



A and C (+), B and D (-)

FLOW CALCULATION


The actual flow is dependent upon electrical command signal and valve pressure drop. The flow for a given valve pressure drop can be calculated using the square root function for sharp edge orifices.

$$Q = Q_{N} \cdot \sqrt{\frac{\Delta p}{\Delta p_{N}}}$$

 $\begin{array}{ll} \textbf{Q} \, [\text{l/min} \, (\text{gpm})] & \text{actual flow} \\ \textbf{Q}_{\text{N}} \, [\text{l/min} \, (\text{gpm})] & \text{rated flow} \end{array}$


 $\begin{array}{ll} \Delta p \left[bar(psi) \right] & \text{actual pressure drop per spool land} \\ \Delta p_{N} \left[bar(psi) \right] & \text{rated pressure drop per spool land} \end{array}$

Flow diagram




NULL CUT OPTIONS

Standard Axis Cut




Minimal change in gain through null region. Best overall preformance for most closed loop systems.

Underlapped



Null region flow gain is higher than normal. Always allows some small amount of flow past the spool.

Overlapped



Null region flow gain is lower than normal. Spool types can range from minimal overlap to completely blocked flow.

RELATED PRODUCTS

DIN Rail Modules - Analog Control Cards

Moog's DIN rail mounted module analog control cards are ideal for use in enclosures where space is limited. Modules include servoamplifers, transducer conditioning electronics, command and auxilliary function modules, valve drive amplifiers, and power supplies. All of these modules are CE marked and require a 24 $\rm V_{\rm DC}$ supply. The modules mount to standard 35 mm DIN rail mount for easy installation and removal.

Portable Valve Testers - Evaluates Valves in the Field

Valve testers are a cost effective method for evaluating valves in the field. They provide a quick and easy means of differentiating between hydraulic and electronic problems.

There are five models to choose from, each with different levels of capability and flexibility to meet your specific requirements. All valve testers have a compact, easily portable design.

Mounting Manifolds - Easier Installation and Maintenance

Various mountings manifolds are available for standard industrial valves, including base and adapter types for mounting and flushing requirements. Other hardware such as bolts and connectors are also available.

The specific accessories you may need for a particular model are listed in the relevant product catalogs and can be ordered through your local office.

Filtration - Oil Filtration Requirements for Industrial Servo Systems

The most effective way to reduce life cycle costs of an oil hydraulic system is through close attention to contamination control.

For industrial servo systems the ideal system filter arrangement is summarized as follows:

- Use a 15 micron (Beta 15 ≥ 75) high pressure filter without by-pass just before the valve or critical parts of the valve (e.g. pilot)
- Use a 3 micron (Beta $3 \ge 75$) low pressure filter in the return or bypass line.
- Use a filter in the tank breather that is at least the same filtration level as the finest filter in the system.

This recommendation is based on the fact that most servo and proportional valves can accept the odd particle up to 25 microns so the pressure filter will protect the valve from catastrophic failure. The real work is done by the low pressure filter reducing small particle contamination which is the prime contributor to component wear and silting.



DIN Rail Module





Mounting Manifolds

Assuming that the filters are properly dimensioned and care is taken during initial installation and maintenance, the aim should be to limit oil contamination to 16/13 (under the old ISO 4406) or 19/16/13 (under the new ISO 4406).

For long life, the maximum levels per the old and new ISO are 15/12 and 18/15/12, respectively. It is important to note that these are maximum contamination levels and with proper care and regular filter change, significantly lower levels can and should be achieved. Attention must also be paid to a number of other factors that contribute to oil condition problems such as elevated temperatures, high tank humidity, "dirty" new oil.

ABOUT MOOG

Moog Inc. is a worldwide designer, manufacturer and integrator of precision control components and systems. Moog's Industrial Group designs and manufactures high performance motion control solutions combining electric, hydraulic, and hybrid technologies with expert consultative support in a range of applications including energy production and generation machinery, industrial production machinery and simulation and test equipment. We help performance-driven companies design and develop their next-generation machines. Moog Industrial Group, with fiscal year 2011 sales of USD 629 million and over 40 locations worldwide, is part of Moog Inc. (NYSE:MOG.A and MOG.B) which has sales of USD 2.3 billion.

Moog maintains facilities in 26 countries around the globe. This vast scope ensures that our engineers remain close to the needs of machine builders and provide flexible design solutions and technical expertise tailored to our customers' toughest challenges.

Moog experts work in close collaboration with machine builders and application engineers to design motion control systems for greater productivity, higher reliability, superior connectivity, less costly maintenance and more effective operations. Our regional presence, industry knowledge and design flexibility ensures Moog motion control solutions are tailored to their environment—from meeting operating regulations and performance standards, to taking machine performance to a higher level.

Products

At the heart of every Moog solution is an array of products engineered for precision, high performance and reliability. For more than six decades, Moog products have been specified for critical machine applications.

Some are developed specifically for unique operating environments. Others are standard equipment on machines across many industries. All are continuously improved to take advantage of the latest technology breakthroughs and advancements.

Moog products include:

- Servo Valves and Proportional Valves
- Servo Motors and Servo Drives
- Servo Controllers and Software
- Radial Piston Pumps
- Actuators
- Integrated Hydraulic Manifold Systems and Cartridge Valves
- Slip Rings
- Motion Bases



Servo Valves



Active Cartridge Valves



Radial Piston Pumps



Servo Drives

Rev. P, March 2024 15

ABOUT MOOG

Solutions

Hydraulic solutions

Since Bill Moog invented the first commercially viable servo valve in 1951, Moog has set the standard for world-class hydraulic technology. Today, Moog products are used in a variety of applications - providing high power, enhanced productivity and ever better performance for some of the worlds most demanding applications.

Electric solutions

Clean operation, low noise generation, less maintenance and reduced power consumption make Moog electric solutions ideal for applications worldwide. Moog is the ideal partner for applications where transitioning technologies requires special expertise.

Hybrid solutions

By incorporating the advantages of existing hydraulic and electric technologies - including modular flexibility, increased efficiency and cleanliness - into innovative hybrid solutions, Moog offers new performance potential in specialized applications.

Moog Global Support

Moog Global Support is our promise to offer world-class Repair and Maintenance Services delivered expertly by our trained technicians. With the reliability only available from a leading manufacturer with facilities around the world, Moog offers you service and expertise you can count on to keep your equipment operating as it should.

This promise offers many benefits to our customers including:

- Reduce your downtime by keeping critical machines running in peak performance
- Protect your investment by ensuring reliability, versatility and long-life of products
- Better plan your maintenance activities and make systematic upgrades
- Leverage our flexible programs to meet the unique service requirements of your facility

Look to Moog for global support including:

- Repair services using OEM parts are performed by trained technicians to the latest specifications
- Stock management of spare parts and products to prevent unplanned downtime



Flight Simulation



Formula One Simulation Table

- Flexible programs, tailored to your needs such as upgrades, preventative maintenance and annual/multiyear contracts
- On-site services bring the expertise to you, providing quicker commissioning, set-up and diagnostics
- Access to reliable services that are guaranteed to offer consistent quality anywhere in the world

For more information on Moog Global Support visit www.moog.com/industrial/service.




Rev. P, March 2024 16

ACCESSORIES AND SPARE PARTS

Part designation	Description	Material	Part number
Maintenance kit	Base o-rings	FKM per AMS7259	B52555RK052K001
	Additional o-rings required for filter access	Note that o-ring material is dependent on application.	
	Filter tube		

ORDERING CODE



All combinations may not be available.

Preferred Models

Model number	Type designation	Rated flow		Rated current
		l/min	gpm	mA
-078-120D	S07F0GM4VBL	75	20	± 40
-078-121D	H07F0GM4VBL	75	20	± 40
-078-130D	S11F0GM4VBL	115	30	± 40
-078-131D	H11F0GM4VBL	115	30	± 40
-078-140D	S15F0GM4VBL	150	40	± 40

Rev. P, March 2024 18

TAKE A CLOSER LOOK.

Moog designs a range of motion control products that complement the performance of those featured in this catalog. Visit our website for more information and contact the Moog facility nearest you.

Australia +61 3 9561 6044 Service + 61 3 8545 2140 info.australia@moog.com service.australia@moog.com

Brazil +55 11 3572 0400 info.brazil@moog.com service.brazil@moog.com

Canada +1 716 652 2000 info.canada@moog.com

China +86 21 2893 1600 Service +86 21 2893 1626 info.china@moog.com service.china@moog.com

France +33 1 4560 7000 Service +33 1 4560 7015 info.france@moog.com service.france@moog.com

Germany +49 7031 622 0 Service +49 7031 622 197 info.germany@moog.com service.germany@moog.com

Hong Kong +852 2 635 3200 info.hongkong@moog.com India +91 80 4057 6666 Service +91 80 4057 6604 info.india@moog.com service.india@moog.com

Ireland +353 21 451 9000 info.ireland@moog.com

Italy +39 0332 421 111 Service 800 815 692 info.italy@moog.com service.italy@moog.com

Japan +81 46 355 3767 info.japan@moog.com service.japan@moog.com

Korea +82 31 764 6711 info.korea@moog.com service.korea@moog.com

Luxembourg +352 40 46 401 info.luxembourg@moog.com

The Netherlands +31 252 462 000 info.thenetherlands@moog.com service.netherlands@moog.com Russia +7 8 31 713 1811 Service +7 8 31 764 5540 info.russia@moog.com service.russia@moog.com

Singapore +65 677 36238 Service +65 651 37889 info.singapore@moog.com service.singapore@moog.com

South Africa +27 12 653 6768 info.southafrica@moog.com

Spain +34 902 133 240 info.spain@moog.com

Sweden +46 31 680 060 info.sweden@moog.com

Turkey +90 216 663 6020 info.turkey@moog.com

United Kingdom +44 (0) 1684 858000 Service +44 (0) 1684 278369 info.uk@moog.com service.uk@moog.com

USA +1 716 652 2000 info.usa@moog.com service.usa@moog.com

For product information, visit www.moog.com/industrial
For service information, visit www.moogglobalsupport.com

Moog is a registered trademark of Moog Inc. and its subsidiaries. All trademarks as indicated herein are the property of Moog Inc. and its subsidiaries. ©2021 Moog Inc. All rights reserved. All changes are reserved.

Catalog, Flow Control Servo Vales, 78 Series STS/Rev. P, March 2024, CDL6272-en

