

TWO STAGE PROPORTIONAL VALVES FOR INDUSTRIAL APPLICATIONS



J866 Series flow control proportional valves are throttle valves for 3- and preferably 4-way applications. They are a high performance, two-stage design that covers the range of rated flows from 10 to 80 L/min at 7.0 MPa valve drop. The output stage is a closed center, four-way, sliding spool. The pilot stage is a symmetrical double-nozzle and flapper, driven by a double air gap, dry torque motor. The spool position is proportional to the coil current. The valve design is simple and rugged for dependable, long life operation. These valves are suitable for Press Machines and other applications with high stability and high repeatability.

TABLE OF CONTENTS

Principle of operation	3
General technical data	4
Technical data	5
Installation drawing	6
Electrical connections Ordering information Spare parts and accessories	7




PRINCIPLE OF OPERATION J866 SERIES

Principle of operation

An electrical command signal is applied to the torque motor coils and creates a magnetic force, which acts on the ends of the
pilot stage armature.

- This causes a deflection of armature / flapper assembly within the flexure tube. Deflection of the flapper restricts fluid flow through one nozzle, which is carried through to one spool end, displacing the spool.
- Movement of the spool opens the supply pressure port (P) to one control port while simultaneously opening the tank port (T) to the other control port. The spool motion also applies a force to the coil spring.
- Once the coil spring force becomes equal to the nozzle pressure difference, and the spool is held open in a state of equilibrium until the command signal changes to a new level.

In summary, the spool position is proportional to the input current. With constant pressure drop across the valve, flow to the load is proportional to the spool position.



- 1 Connector
- 2 Lower polepiece
- 3 Flapper
- 4 Inlet filter
- 5 Coil spring
- 6 Return port (T)
- 7 Spool
- 8 Control port (B)
- 9 Pressure port (P)
- 10 Control port (A)
- 11 Inlet orifice
- 12 Nozzle
- 13 Magnetic null adjuster
- 14 Flexure tube
- 15 Coil
- 16 Upper polepiece
- 17 Armature

Valve Features

- 2-stage design with dry torque motor
- High resistance to contamination by larger internal clearance & longer spool stroke
- Low friction double nozzle pilot stage
- High spool control forces
- Rugged, long-life design

The actual flow is dependent upon electrical command signal and valve pressure drop. The flow for a given valve pressure drop can be calculated using the square root function for sharp edge orifices:

$$Q=Q_N \sqrt{\frac{\Delta P}{\Delta P_N}}$$

 $\begin{array}{l} Q \ L/min = calculated \ flow \\ Q_N \ L/min = rated \ flow \\ \Delta P \ MPa = actual \ valve \ pressure \ drop \\ \Delta P_N \ MPa = rated \ valve \ pressure \ drop \end{array}$

General Technical Data

Proof Pressure

P, A and B port 31.5 MPa (Static pressure)
T port 21.0 MPa (Static pressure)

Temperature Range

Fluid $-10 \sim 80\,^{\circ}\mathrm{C}$ Ambient $-10 \sim 80\,^{\circ}\mathrm{C}$

Seal Material

NBR

Other seal material upon request

Operating Fluid

Compatible with common hydraulic fluids, other fluids on request.

Recommended Viscosity

 $10 \sim 400 \, \text{mm}^2/\text{s}$

System Filtration

High pressure filter (without bypass, but with dirt alarm) mounted in the main flow and if possible, directly upstream of the valve. Refer to Moog filtration catalog for recommended filtration scheme.

Class of Cleanliness

The cleanliness of the hydraulic fluid greatly effects the performance (spool positioning, high resolution) and wear (metering edges, pressure gain, leakage) of the valve.

Recommended Cleanliness Class

 $\begin{array}{ll} \mbox{For normal operation} & \mbox{ISO}\,4406 \!\leq\! 14/11 \\ \mbox{For longer life} & \mbox{ISO}\,4406 \!\leq\! 13/10 \end{array}$

Filter Rating

Recommended

For normal operation $\beta_{10} \ge 75 \ (10 \ \mu \text{m absolute})$ For longer life $\beta_5 \ge 75 \ (5 \ \mu \text{m absolute})$

Installation Operations

Any position, fixed or movable

Vibration


10 g, 3 axes

Weight

2.1 kg

Shipping Plate

Delivered with an oil sealed shipping plate.



Valve Flow Diagram


Valve flow for maximum valve opening (100% command signal) as a function of the valve pressure drop.

TECHNICAL DATA J866 SERIES

Technical Data

		Specification	Condition
Rated Supply Pressure		21.0 MPa	
Operating Pressure Range		7 ~ 21.0 MPa	
Proof Pressure (Supply)		31.5 MPa	
Proof Pressure (Return)		21.0 MPa	
Rated Current (Series connection)		±10 mA	
Nominal Coil Resistance		200 Ω / coil	
Null Bias		< ±3%	Test Pressure 21 MPa
Null Shift		< 3.0 %	Temperature ($\Delta T = 30 ^{\circ}\text{C}$: $25 \sim 55 ^{\circ}\text{C}$)
		< 3.0 %	Supply Pressure (30 % of Rated Pressure)
Hysteresis		< 4.0 %	@ 200 Hz 20% _{P-P}
Frequency Response	Amplitude Ratio — 3dB	> 30 Hz	Supply Pressure 21 MPa,
	90°phase lag	> 50 Hz	±25% input
Temperature Range		−10 ~ 80 °C	
Operating Fluid			Petoroleum base hydraulic fluid
Viscosity Range of Operating Fluid		$10\sim400\mathrm{mm}^2/\mathrm{s}$	Petoroleum base hydraulic fluid
Connector Direction		BPort	
Weight		2.1 kg	

No-Load Flow Gain Characteristic



Supply Pressure


—— 21 MPa — — 14 MPa —— 7 MPa

--- 3.5 MPa

Dither Signal


200 Hz, 4 mA p-p

Change in Control Flow with Current and Load Pressure




INSTALLATION DRAWING J866 SERIES

Installation Drawing



Note: The mounting manifold must conform to DIN 24340 A $10\,$

Mounting Manifold



Electrical Connections

Rated current and coil resistance

Only one type is available for J866 Series Proportional valves.

Coil connections

A four-pin electrical box connector (that mates with an MS31 06A-14S-2S cable connector) is standard. All four torque motor leads are available at the connector so external connection can be made for series, parallel or single coil operation.

Servoamplifier

The servoamplifier responds to input current, so a servoamplifier that has high internal impedance (as obtained with current feedback) should be used. This will reduce the effects of coil inductance.

Electrical Connections (Examples with typical J866 Series coil)

	· 1 /1			
	Parallel	Series	Single	
	A B C D	A B C D	$ \begin{array}{c c} R & R \\ \hline NO & NO \\ A & B & C & D \\ \downarrow i_1 & \downarrow & \downarrow j_2 \end{array} $	
Coil Resistance	100 Ω	400 Ω	200 Ω	
Rated Current	±20 mA	±10 mA	±20 mA	
Coil Inductance	1.5 H	4.7 H	1.6 H	
Electrical Power	0.04 W	0.04 W	0.0.8 W	
Polarity for valve opening	$P \rightarrow A, B \rightarrow T$ A and C (+), B and D (-)	$P \rightarrow A, B \rightarrow T$ A (+), D (-)	$P \rightarrow A, B \rightarrow T$ A (+), B (-) or C (+), D (-)	

Ordering Information


Standard Models

Model	Rated Flow Valve Drop 7.0MPa	Internal Leakage System Pressure 21.0 MPa	Rated Current (Series Connection)	Nominal Coil Resistance
J866 - 1000	10 L/min	1.3 L/min	10 mA	200 Ω
J866 - 1001	20 L/min	1.6 L/min	10 mA	200 Ω
J866 - 1002	40 L/min	2.2 L/min	10 mA	200 Ω
J866 - 1003	60 L/min	2.8 L/min	10 mA	200 Ω
J866 - 1004	80 L/min	3.4 L/min	10 mA	200 Ω

Spare parts and Accessories

Part	Size	Part Number
0 - Rings (included in delivery) P, A, B, T	AS568-014	A47622 - 004
Mounting Bolts (included in delivery)	M6 × 60 mm (4 pieces)	A04001 - 006 - 060
Mating Connector		MS3106A14S2S (MS3106A - 14S - 2S)
Clamp for Mating Connector		MS3057 - 6A
Flushing Block		C92092 - 001

Model Number



FOR MORE SPECIFIC INFORMATION

For more specific information regarding Moog products, solutions or services, please Email us, or visit our website. You may also directly contact your local Moog office.

Argentina +54 11 4326 5916 info.argentina@moog.com

Australia +61 3 9561 6044 info.australia@moog.com

Brazil +55 11 3572 0400 info.brazil@moog.com

Canada +1 716 652 2000 info.canada@moog.com

China +86 21 2893 1600 info.china@moog.com

Finland +358 10 422 1840 info.finland@moog.com

France +33 1 4560 7000 info.france@moog.com

Germany +49 7031 622 0 info.germany@moog.com

Hong Kong +852 2 635 3200 info.hongkong@moog.com India +91 80 4057 6666 info.india@moog.com

Ireland +353 21 451 9000 info.ireland@moog.com

+39 0332 421 111 info.italy@moog.com

Japan +81 46 355 3767 info.japan@moog.com

Korea +82 31 764 6711 info.korea@moog.com

Luxembourg +352 40 46 401 info.luxembourg@moog.com

The Netherlands +31 252 462 000 info.thenetherlands@moog.com

Norway +47 6494 1948 info.norway@moog.com

Russia +78317131811 info.russia@moog.com Singapore +65 677 36238 info.singapore@moog.com

South Africa +27 12 653 6768 info.southafrica@moog.com

Spain +34 902 133 240 info.spain@moog.com

Sweden +46 31 680 060 info.sweden@moog.com

Switzerland +41 71 394 5010 info.switzerland@moog.com

Turkey +90 216 663 6020 info.turkey@moog.com

United Kingdom +44 168 429 6600 info.uk@moog.com

USA +1 716 652 2000 info.usa@moog.com

www.moog.co.jp/

Moog is a registered trademark of Moog Inc. All trademarks as included herein are the property of Moog Inc. and its subsidiaries.

©2012 Moog Inc. All rights reserverd.

J866 Series-en YCO / YCO / PDF, Jan 2013

