

Sandwich plate valve with flow control function (01/2017)


Sandwich plate valve with flow control function (ZFM2RP06)

SIZE: ISO 4401-03-02-0-05

Operating principle

The ZFM2RP06 is a sandwich plate valve with a flow control function in port A. The flow control function is active for flows from port A1 to Port A2. Parallel to the flow control valve is a bypass check valve enabling free flow port A2 to Port A1.





Advantages

- Maximum operating pressure: 420 bar
- Flow rates available in multiple orifice configurations from 0.4 to 6.0 l/min. The flow rate is adjusted by changing out the installed orifice.
- Results in a very soft unloading function, without any loss in closing time, when used as a pilot valve to control a 2-way slip-in cartridge valve
- Flow control function in a compact sandwich plate design
- Can be combined with other sandwich plate valves, directional valves and control covers to achieve more complex control functions.
- Threads in the P, A2, B and T ports enable further orifices to be used if needed.







Applications

The ZFM2RP06 sandwich plate valve can be used as a flow control valve with bypass check valve in port A for a maximum controlled flow of 6 l/min.

In combination with an RM* cartridge cover and an appropriate pilot valve; the ZFM2RP06 can be used to control a 2-way slip in cartridge.

When used in this fashion, the flow control valve will vent the pilot oil from the cartridge valve at constant flow rate independent of the pressures present. Depending on the diameter of the flow control orifice used, this vented flow will be between 0.4 and 6 l/min. Allowing the cartridge valve to open in a uniform and controlled manner; resulting in a soft unloading of the hydraulic system.

In the opposite direction, the flow of pilot oil to the cartridge valve will bypass the flow control orifice. This will result in a rapid closing of the cartridge valve independent of the flow control orifice used.

Figure 4 (page 6) shows an example of a soft unloading pressure valve.



Flow control orifice determines the flow rate through the valve


Figure 1: Location of flow control orifice

* see catalog "Cartridge Covers ISO 7368 Sizes 16 to 100"



General Data	Value	Unit	Specification
Valve type	-	-	Direct operating sandwich plate valve
Mounting type	-	-	Subplate mounting
Mounting orientation	-	-	any
Size (port pattern)	-	-	ISO 4401-03-02-0-05
Ambient temperature range	min.	°C	-30
Ambient temperature range	max.	С°	+80
Weight	m	kg	1,6
Hydraulic			
Max. operating pressure	P,A,B, T	MPa	42
Max. flow rate	Q _{max}	l/min	 6 : from port A1 to port A2 (flow control function) 35 : from port A2 to port A1 (via bypass check valve)
Seals* for hydraulic fluids	-	-	N (NBR) : Mineral oil based hydraulic fluids; HFB,HFC type fluids Seals for other hydraulic fluids on request
Hydraulic fluid	min.	°C	-30
temperature range	max.	°C	+80
Viceosity	min.	mm²/s	2,8
Viscosity range	max.	mm²/s	380
Cleanliness class according to ISO Code	max.	-	ISO 4406 (C), class 20/18/15

Bypass check valve performance curve







Selection of the flow control orifice

The following performance curves can be used to select the proper flow control orifice. The desired flow rates shown on the left hand side of the graph line up nicely with the orifice sizes shown on the right hand side thanks to the pressure independent characteristics of this valve. The largest orifice, with a diameter of 2.5 mm, will result in a constant flow of 6 l/min where as an 1.5 mm orifice will result in a constant flow of 3 l/min.

In comparison, a conventional cartridge valve orifice configuration would require a 0.65mm orifice to produce a pilot oil flow of ca. 3,0 l/min at a $\Delta p = 200$ bar. In short, the ZFM2RP06 is able to provide the same pilot oil flow rate using a much larger orifice diameter. This has the addition advantage of creating a more robust hydraulic system.




Figure 3: Performance in relation to the installed flow control orifice

A soft unloading pressure valve

Figure 4 shows an example of soft unloading pressure valve, with a pressure relief function, using a ZFM2P06 sandwich valve.

A directional pilot valve and RM cartridge cover complete the stack; resulting in a very cartridge valve capable of a very soft, pressure independent unloading. The bypass check valve ensures that a rapid closing of the valve is still possible. Figure 5 shows the soft unloading capabilities of this type of configuration.

In general, every cartridge valve can profit from a soft unloading function like this.






Figure 4: A soft unloading pressure valve (closed when de-energized)

Unloading function

Pressure unloading A \Rightarrow B in relation to the pilot valve control signal over time, measured at T = 45°C





Port pattern according to ISO 4401-03-02-0-05

Required surface finish of mating part





Figure 6: Dimensions





Ordering Codes (Example)					
Flow of [I/min]	Description	Part Number			
0,4	N-ZFM2RP06K4K0AS/K06;S04	XZB10319-006N01			
0,7	N-ZFM2RP06K4K0AS/K08;S07	XZB10319-008N01			
1,3	N-ZFM2RP06K4K0AS/K10;S13	XZB10319-013N01			
1,9	N-ZFM2RP06K4K0AS/K12;S19	XZB10319-019N01			
3,0	N-ZFM2RP06K4K0AS/K15;S30	XZB10319-030N01			
4,4	N-ZFM2RP06K4K0AS/K18;S44	XZB10319-044N01			
5,0	N-ZFM2RP06K4K0AS/K20;S50	XZB10319-050N01			
6,0	N-ZFM2RP06K4K0AS/K25;S60	XZB10319-060N01			



Seal Kits*				
Pos.	Qty.	Description	Part Number	
1	1	Complete seal kit; NBR 90 Shore	XZB10319D000N00	
2	4	O-Ring NBR 9,25 x 1,78		

*Seal kits for other hydraulic fluids on request




Figure 7: Seal positions

Accessories (must be ordered separately)					
Pos.	Description	Part number			
	A selection of orifices available for ports P,A,B,T*				
See page 7	Orifice – metric ISO 4026-M6x6x0,6	CA37690-060			
	Orifice – metric ISO 4026-M6x6x0,8	CA37690-080			
	Orifice – metric ISO 4026-M6x6x1,0	CA37690-100			
	Orifice – metric ISO 4026-M6x6x1,2	CA37690-120			
	Orifice – metric ISO 4026-M6x6x1,5	CA37690-150			
	Orifice – metric ISO 4026-M6x6x2,0	CA37690-200			

*other orifices available on request







As a recognized leader in motion control technologies, Moog offers a full range of services to support our products and ensure that they meet the expectations of customers. Moog experts are the best at helping customers select the right products and ensuring that they run reliably for a long time.

When it is time for new machine commissioning, refurbishment or routine maintenance, our engineers can help to optimize machine performance, minimize downtime and ensure the smooth application of our products.

Moog Authentic Repair[™] is designed to provide the highest quality repair services using original equipment parts, the latest design specifications, and highly trained technicians. This ensures that our repaired products will run as well as when they were new.

With facilities in over 25 countries, Moog is committed to offering convenient local service to our customers.

Visit www.moog.com/industrial/worldwide to find the location nearest you for appli-cation engineering, repair, or field services.

FOR MORE INFORMATION VISIT http://www.moog.com/industrial



MORE PRODUCTS. MORE SUPPORT.

Moog designs a range of motion control products to complement those featured in this document. Moog also provides service and support for all of our products. For more information, contact the Moog facility closest to you.

Australia +61 3 9561 6044 Service + 61 3 8545 2140 info.australia@moog.com service.australia@moog.com

Brazil +55 11 3572 0400 info.brazil@moog.com service.brazil@moog.com

Canada +1 716 652 2000 info.canada@moog.com

China +86 21 2893 1600 Service +86 21 2893 1626 info.china@moog.com service.china@moog.com

France +33145607000 Service +33145607015 info.france@moog.com service.france@moog.com

Germany +49 7031 622 0 Service +49 7031 622 197 info.germany@moog.com service.germany@moog.com

Hong Kong +852 2 635 3200 info.hongkong@moog.com India +91 80 4057 6666 Service +91 80 4057 6604 info.india@moog.com service.india@moog.com

Ireland +353 21 451 9000 info.ireland@moog.com

Italy +39 0332 421 111 Service 800 815 692 info.italy@moog.com service.italy@moog.com

Japan +81 46 355 3767 info.japan@moog.com service.japan@moog.com

Korea +82 31 764 6711 info.korea@moog.com service.korea@moog.com

Luxembourg +352 40 46 401 info.luxembourg@moog.com

The Netherlands +31 252 462 000 info.thenetherlands@moog.com service.netherlands@moog.com Russia +7 8 31 713 1811 Service +7 8 31 764 5540 info.russia@moog.com service.russia@moog.com

Singapore +65 677 36238 Service +65 651 37889 info.singapore@moog.com service.singapore@moog.com

South Africa +27 12 653 6768 info.southafrica@moog.com

Spain +34 902 133 240 info.spain@moog.com

Sweden +46 31 680 060 info.sweden@moog.com

Turkey +90 216 663 6020 info.turkey@moog.com

United Kingdom +44 (0) 1684 858000 Service +44 (0) 1684 278369 info.uk@moog.com service.uk@moog.com

USA +1 716 652 2000 info.usa@moog.com service.usa@moog.com

For product information, visit **www.moog.com/industrial** For service information, visit **www.moogglobalsupport.com**

Moog is a registered trademark of Moog Inc. and its subsidiaries. All trademarks as indicated herein are the property of Moog Inc. and its subsidiaries. ©2017 Moog Inc. All rights reserved. All changes are reserved.

Sandwich plate valve with flow control function (ZFM2RP06) Moog Luxembourg/Rev. C, February 2017

MOOG