

2-Way Spool Type Pressure Reducing Valve Series D (06/2014)

2-Way Spool Type Pressure Reducing Valve (DMO) ISO 7368 NB 16 – NB 50

General Description


2-way pressure reducing valves are used to reduce a variable input pressure (primary pressure at B) to a lower, constant output pressure (secondary pressure at A).

The reduced pressure can be set using a pressure relief valve on the valve cover. Depending on configuration, this valve can also function as a pressure compensator.

The preferred mode of mounting is the manifold block which, depending on the hydraulic circuit for the specific application, can be equipped with several interconnected valves.

The valves are available as "normally open" or "normally closed" versions.





Benefits

- Maximum operating pressure: 350 bar
- Improved flow characteristics compared to series B
- Can be used with standard series D covers (RM or 1W)
- Available in multiple configurations

Sizes

- NB 16
- NB 25
- NB 32
- NB 40
- NB 50




Operating Principle

A DMO type pressure reducing valve is a spool type valve without an effective surface in port B. The effective surfaces in port C and in operational port A are of equal size (surface ratio 1:1). The flow direction is from B to A.

As port B is pressurized, oil will flow from B to A. As the pressure in port A approaches the set pressure value of the limiting valve, the spool will move towards the closed position throttling the oil flow. As the pressure in port A exceeds the set pressure value, the spool will close port A and the oil flow will be interrupted.

Depending on the hydraulic circuit and the adaptation of suitable standard covers; a DMO type valve can also be used, for example, in flow-control functions as a pressure compensator.



Specification

General data	Value	Unit	Specification						
Mode of Construction	-	-	2-Way Spool Type Pressure Reducing Valve						
Туре	-	-	DMO (Manual Pressure Adjustment)						
Design	-	-	Cartridge Valve						
Mounting style	-	-	Manifold Cartridge Mounting						
Nominal size	NB	-	16	25	32	40	50		
Mounting dimensions according ISO 7368	-	-	BA-06-2-A	BB-08-2-A	BC-09-2-A	BD-10-2-A	BE-11-2-A		
Mounting position	-	-	Any						
Flow Direction	-	-	B → A						
Operating pressure	max.	MPa	35						
Ambient temperature	min.	°C	-30						
range	max.	°C	+80	+80					
				→ M-DN	/IO, hydraulic	fluids on mir	neral oil basis		
Seals* for hydraulic fluids	-	-	FKM → V-DMO, hydraulic fluids on mineral oil basis, HFD-hydraulic fluids						
			NBR → N-DMO, hydraulic fluids on mineral oil basis, HFC-hydraulic fluids						
Hydraulic fluid		•••	-30 to +80	NBR					
temperature range	-	°C	-10 to +80 FKM + PU						
	min.	mm²/s	2,8						
Viscosity range	max.	mm²/s	380						
Operating viscosity	-	mm²/s	15 to 45						
Cleanliness to ISO-Code	max.		ISO 4406 (C) class 20/18/15						


* PU: Polyurethane; FKM: Fluorosilicone rubber (Viton[®]); NBR Nitrile rubber (Buna N); Other hydraulic fluids on request




Basic Configuration

(1) Pressure reducing valve

- Standard RM cover
- Pilot oil supply from cartridge port A through cover port X
- Without sandwich cover (max 3 bar spring)
- NB 16 to NB 40





- Standard RM cover
- Pilot oil supply from cartridge port A through cover port X
- With sandwich cover for 8 bar spring
- NB 16 to NB 40 (NB 50 with 3 bar spring)



(3) Pressure reducing valve


- Standard 1W cover
- Pilot oil supply from cartridge port B through 2-way flow controller
- port Y connected to tank
- NB 16 to NB 50
- Higher flow rates possible compared to configurations (1) and (2)





(4) Pressure compensator valve (upon request)


- Standard RM cover
- Pilot oil supply from cartridge port B through 2-way flow controller
- port Y as pressure load tap downstream of the throttle valve
- NB 16 to NB 40 (NB 50 with sandwich cover)







Characteristic Curves

Conditions: system pressure 350 bar, oil temperature 40 °C, oil viscosity 32 cSt (Blue = performance limit with 3 bar spring, Red = performance limit with 8 bar spring)











Characteristic Curves

Conditions: system pressure 350 bar, oil temperature 40 °C, oil viscosity 32 cSt (Red = performance limit with 0,5 bar spring)



Dimensions



	NB 16	NB 25	NB 32	NB 40	NB 50 ²⁾
H1 [mm]	82	87	92	106	166 ³⁾
H2 [mm]	35	40	45	60	120 ³⁾
H3 [mm]	23	22	26	39	99 ³⁾
H4 [mm]	-	-	27	30	90 ³⁾
H5 [mm]	47	52	57	72	182 ³⁾
B1 [mm]	80 ¹⁾	85	102	125	140
B2 [mm]	65	85	102	125	140
L1 [mm]	9,5	13,5	16	20	20
L2 [mm]	9,5	13,5	16	20	20
L3 [mm]	7	23,5	32	43,5	51
L4 [mm]	16,25	26,25	34,65	46,25	53,75
L5 [mm]	-	-	3,5	4,5	4,5
Plugs MX	-	-	G 1/8"	G 1/4"	G 1/4"
Mounting Screws ISO 4762-12.9	M8x35	M12x40	M16x50	M20x70	M20x130
Tightening Torque [Nm]	30	100	300	550	550
Weight [kg]	2,9	3,9	5,5	9,6	20,7


¹⁾ Dimension B1 is larger than specified by ISO 7368 ²⁾ NB50 delivered standard with sandwich cover (H1=166 mm)

³⁾ For NB50 with 0,5 bar spring subtract 60 mm from dimension given



Options


Option: Sandwich cover for 8 bar spring NB16...NB40 (NB50 using max. 3 bar spring)



	NB 16	NB 25	NB 32	NB 40	NB 50
H1 [mm]	30	40	70	90	60
B1 [mm]	80	85	102	125	140
B2 [mm]	65	85	102	125	140
L1 [mm]	9,5	13,5	16	20	20
L2 [mm]	9,5	13,5	16	20	20
Weight [kg]	0,9	2	4,8	9,3	7,2

Ζ2

Option: 2-way flow control (NB06) using a sandwich plate (weight 1,25 kg)






Alternative configurations for pilot valves that do not use port A.


It is recommended that pilot valves with no connection to port A be used in combination with a sandwich plate (P connected to A).

Standard:

Moog DB pilot valve + RM cover





Alternative: DB pilot valve + sandwich cover + RM cover



Valve configurations using a flow control sandwich plate, regardless of pilot valve; do not require any special sandwich plates.

Option: Sandwich cover (NB06) with connections from P and A (weight 0,7 kg)








Ordering Information

M - D MO E 40 D	L 6 M X 2 G /
Seal material	Options
M FPM/FKM + PUR	example: A10 = 1,0 orifice in port A of cover
	example: B12 = 1,2 orifice in port B of cover
Valve type	EP_ Pressure setting (adjustment 8 only)
D Pressure valve	MC_ With flow control valve sandwich cover
Valve function	
CO Pressure compensator, manual adjust	Spring pilot valve
MO Pressure reducing valve, manual adjust	B 70 bar
	E 175 bar
Mounting	G 245 bar
E Manifold mounting	K 350 bar
ik zi	
Size	
16 NB16	27
25 NB25	Adjustment
32 NB32	2 Allen head screw with jam nut
40 NG40	8 Same as 2, with cap + safety
50 NG50	
Serial number	
D	
Our days	Pilot oil supply
Spring	X X and Y through mounting surface
R ¹¹ 0,5 bar	
L 3,0 bar	
W 8,0 bar 0.5 bar spring only in combination with a flow control sandwich plate	
	Function
Series	M normally open
6 Cavity according to ISO 7368	N ²⁾ normally closed
	²⁾ Version N (normally closed) only available upon request

Order Example

2/2-Way pressure reducing valve, NB 32, manual pressure adjustment, normally open

$\underline{M}\text{-}DMOE32D\underline{L}6\underline{M}\underline{X}\underline{2}\underline{P}/\underline{A10};\underline{P12}$





Order Numbers

|--|

Function: normally open; Adjustment method 2, Spring pilot valve 350 bar, Seals PUR/FKM

	• •	-		
Symbol	Size	Spring	ZWD*	Type code
	16	3 bar	-	M-DMOE16DL6MX2K
	10	8 bar	×	M-DMOE16DW6MX2K
	25	3 bar	-	M-DMOE25DL6MX2K
	25	8 bar	×	M-DMOE25DW6MX2K
	32	3 bar	-	M-DMOE32DL6MX2K
		8 bar	×	M-DMOE32DW6MX2K
Рв	40	3 bar	-	M-DMOE40DL6MX2K
	40	8 bar	×	M-DMOE40DW6MX2K
	50	3 bar	×	M-DMOE50DL6MX2K
		8 bar	-	not available
*ZWD = sandv	vich cov	er require	d	

Pressure reducing valve with sandwich cover flow control valve (1W cover)

Function: normally open; Adjustment method 2, Spring pilot valve 350 bar, Seals PUR/FKM

Symbol	Size	Spring	ZWD*	Type code		
	16	0,5 bar	-	M-DMOE16DR6MX2K/MC_		
	10					
	25	0,5 bar	-	M-DMOE25DR6MX2K/MC_		
	20					
	32	0,5 bar	-	M-DMOE32DR6MX2K/MC_		
	40 0,5	0,5 bar	-	M-DMOE40DR6MX2K/MC_		
	50	0,5 bar	-	M-DMOE50DR6MX2K/MC_		
	50					
* no sandwich cover required for these valve types						

As a recognized leader in motion control technologies, Moog offers a full range of services to support our products and ensure that they meet the expectations of customers. Moog experts are the best at helping customers select the right products and ensuring that they run reliably for a long time.

When it is time for new machine commissioning, refurbishment or routine maintenance, our engineers can help to optimize machine performance, minimize downtime and ensure the smooth application of our products.

Moog Authentic Repair ServiceTM is designed to provide the highest quality repair services using original equipment parts, the latest design specifications, and highly trained technicians. This ensures that our repaired products will run as well as when they were new.

With facilities in over 25 countries, Moog is committed to offering convenient local service to our customers.

Visit www.moog.com/industrial/worldwide to find the location nearest you for application engineering, repair, or field services.

FOR MORE INFORMATION VISIT http://www.moog.com/industrial



MOOG.COM/INDUSTRIAL

For the office nearest you, contact us online at moog.com/industrial/globallocator.

Argentina	+54	(0) 11 4326 5916
Australia	+61	(0) 3 9561 6044
Austria	+43	(0) 664 144 6580
Brazil	+55	(0) 11 35720400
Canada	+1	716 652 2000
China	+86	(0) 21 2893 1600
Finland	+358	(0) 104221840
France	+33	(0) 1 4560 7000
Germany	+49	(0) 7031 622 0
Hong Kong	+852	2 635 3200
India	+91	(0) 80 4057 6605
Ireland	+353	(0)21 451 9000
Italy	+39	0 332 421111
Japan	+81	(0) 46 355 3767
Korea	+82	(o) 31 764 6711
Luxembourg	+352	40 46 401
Netherlands	+31	(0) 252 462 000
Norway	+47	6494 1948
Russia	+7	8 31 713 1811
Singapore	+65	677 36238
South Africa	+27	(0) 12 653 6763
Spain	+34	902 133 240
Sweden	+46	(0) 31 680 060
Switzerland	+41	(0) 71 394 5010
United Kingdom	+44	(0) 168 429 6600
USA	+1	(1) 716 652 2000

info.argentina@moog.com info.australia@moog.com info.austria@moog.com info.brazil@moog.com info.canada@moog.com info.china@moog.com info.finland@moog.com info.france@moog.com info.germany@moog.com info.hongkong@moog.com info.india@moog.com info.ireland@moog.com info.italy@moog.com info.japan@moog.com info.korea@moog.com info.luxembourg@moog.com info.netherlands@moog.com info.norway@moog.com info.russia@moog.com info.singapore@moog.com info.southafrica@moog.com info.spain@moog.com info.sweden@moog.com info.switzerland@moog.com info.unitedkingdom@moog.com info.usa@moog.com

©2010 Moog Inc.

Moog is a registered trademark of Moog, Inc. and its subsidiaries. All trademarks as indicated herein are property of Moog, Inc. and its subsidiaries. All rights reserved.

DM(K)O_D6-1-EN-Pressure Reducing-Compensator Valves - CDL66633-001-A-06-2014

