

Application Notes

1 Scope

These application notes are a guide to applying the G123-815 Buffer Amplifier. They tell you how to install, connect and adjust the Buffer Amplifier. They do not tell you how to design the closed loop system in which it is used.

2 Description

The G123-815 Buffer Amplifier interfaces between standard PLC analogue input and output modules, on one side, and a position transducer and a Moog valve, on the other. It simplifies the use of a PLC in closing position loops.

The Buffer Amplifier solves the common problem of the $\pm 10V$ PLC output being incompatible with the valve drive requirements. It also provides digital noise filtering for the valve signal and noise filtering for the position transducer signal. For a more detailed description, see Moog brochure G123-815E01.01.


3 Installation

3.1 Placement

A horizontal DIN rail, mounted on the vertical rear surface of an industrial steel enclosure, is the intended method of mounting. The rail release clip of the G123-815 should face down, so the front panel and terminal identifications are readable and so the internal electronics receive a cooling airflow. An important consideration for the placement of the module is electro magnetic interference (EMI) from other equipment in the enclosure. For instance, VF and AC servo drives can produce high levels of EMI. Always check the EMC compliance of other equipment before placing the G123-815 close by.


3.2 Cooling

Vents in the top and bottom sides of the G123-815 case provide cooling for the electronics inside. These vents should be left clear. It is important to ensure that equipment below does not produce hot exhaust air that heats up the G123-815.




3.3 Wiring

The use of crimp "boot lace ferrules" is recommended for the screw terminals. Allow sufficient cable length so the circuit card can be withdrawn from its case with the wires still connected. This enables switch changes on the circuit card to be made while the card is still connected and operating. An extra 100mm, for cables going outside the enclosure, as well as wires connecting to adjacent DIN rail units, is adequate.



Preferred Wiring



Alternative Wiring

3.4 EMC

The G123-815 emits radiation well below the level called for in its CE mark test. Therefore, no special precautions are required for suppression of emissions. However, immunity from external interfering radiation is dependent on careful wiring techniques. The accepted method is to use screened cables for all connections and to radially terminate the cable screens, in an appropriate grounded cable gland, at the point of entry into the industrial steel enclosure. If this is not possible, chassis ground screw terminals are provided on the G123-815. Exposed wires should be kept to a minimum length. Connect the screens at both ends of the cable to chassis ground.



4 Power supply

24V nominal, 22 to 28V

20mA @ 24V without a load, 145mA @ 100mA load.

If an unregulated supply is used, the bottom of the ripple waveform is not to fall below 22V.

5 Set-up adjustments



5.1 Digital noise filter

This filter removes the digital quantization noise, due to the PLC update period, in the PLC output signal. Because PLC's can have low frequency period noise that the valve can respond to, it is important to remove this update rate noise so the valve does not buzz and the load does not follow. The update period of the PLC needs to be known so the correct filter time constant can be selected. Initially set the filter period to be equal to the update rate. Switch values sum, so if you need 15mS, select 10 and 4.7.

When the system is operating, a final check of the time constant can be made. If the valve buzzes, a greater time constant is required. If the valve does not buzz, reduce the time constant until buzzing is detected, then increase it until the buzzing just stops.

To calculate the 3dB frequency roll off point, use the formula:

$$f = \frac{159}{T} \text{ Hz, where } T = \text{the sum of mS period switches selected}$$

5.2 Low Rin

The "low Rin" switch drops the input resistance for the PLC signal from 100k Ohm to 1k Ohm. This can improve the noise immunity of the signal. Be sure the PLC output can deliver $\pm 10\text{mA}$ that is needed when low Rin is selected.

5.3 Valve drive signal

Select the output signal to match the valve requirement. If voltage is selected, the $\pm 10\text{V}$ output can drive up to $\pm 10\text{mA}$. If current is selected, the full scale current output will then need to be selected on the valve current switches. The switches sum, so if 45mA is required, select 30, 10 and 5mA. Maximum output current, in current mode, is $\pm 100\text{mA}$.

6 Test points and indicators

The Iv and Vv LEDs show the polarization and level of the selected output signal.

The valve test point gives the actual voltage on the valve output terminal. When the output signal is selected as current, a knowledge of the valve's input resistance is needed to interpret the test point signal. For instance, if 10mA is selected and a valve with 200 Ohm input resistance is connected, the signal on the valve test point will vary between $\pm 2\text{V}$.


The probe test point enables a check of the filtered position transducer signal.

7 Withdrawing the circuit card from its case

The circuit card needs to be withdrawn from its case to set the digital noise filter switches, to select the output signal type, to select the current and to select low Rin.


To do this, push one tab in with a pen or screwdriver, while gently pulling on the top cover on that side. The cover will release approximately one mm. Repeat on the other side and then withdraw the cover and circuit card until the required switches are exposed. The rigidity of the connecting wires will hold the circuit card in position while the switches are set.

8 Block-wiring diagram




Valve wiring diagrams


8.1 Proportional valve (efb)



8.2 Servovalve (mfb) series coils



8.3 Servovalve (mfb) parallel coils



9 Specifications

Valve drive input: 0 to $\pm 10V$
Valve drive outputs: 0 to $\pm 10V$ @ 1K Ohm min
 0 to $\pm 100mA$ max
 max load = $\left(\frac{11V}{I(Amp)} - 39 \right) Ohm$

Valve drive current selections: $\pm 5, 10, 20, 30$ & $50 mA$

Valve drive test point: $Z_o = 10K Ohm$

Probe test point: $Z_o = 10K Ohm$

Vv LED: Maximum illumination at $\pm 10V$
 + = red
 - = green

Iv LED: Maximum illumination at $\pm 5 mA \setminus \pm 100mA$
 + = red
 - = green

Valve filter type: Active, single pole

Valve filter corner frequency selections: 7, 16, 34, 72 & 723 Hz $\pm 10\%$

Probe filter corner frequency: $154Hz \pm 10\%$

Class of protection: IP 20

Supply: 24 V nominal, 22 to 28 V
 20 mA @ 24 V, no load,
 145 mA @ 100 mA load

Terminal 10 max current: 500 mA

Mounting: DIN rail

Temperature: 0 to $40^{\circ}C$

Dimensions: 100W x 108H x 22.5D

Weight: 120g

CE mark: EN50081.1 emission
 EN50082.2 immunity

C tick: AS4251.1 emission

This page left blank intentionally

Internet Data

For a detailed Data Sheet and the latest version of these Application Notes, please refer to the Moog website www.moog.com/dinmodules

MOOG

Industrial Controls Division. Moog Inc., East Aurora, NY 14052-0018. Telephone: 716/652-3000. Fax: 716/655-1803. Toll Free 1-800-272-MOOG.

Moog GmbH. Germany. Telephone: 07031-622-0. Fax: 07031-622-100.

Moog Sarl. France. Telephone: 01 45 60 70 00. Fax: 01 45 60 70 01.

Moog Australia Pty. Ltd. Telephone: 03 9561 6044. Fax: 03 9562 0246.

Moog pursues a policy of continuous development and reserves the right to alter designs and specifications without prior notice. Information contained herein is for guidance only and does not form part of a contract.

Australia: Melbourne, Sydney, Brisbane ■ Austria: Vienna ■ Brazil: Sao Paulo ■ Denmark: Birkerød ■ England: Tewkesbury ■ Finland: Espoo ■ France: Rungis ■ Germany: Böblingen, Dusseldorf ■ Hong Kong: Shatin ■ India: Bangalore
Ireland: Ringaskiddy ■ Italy: Malnate (VA) ■ Japan: Hiratsuka ■ Korea: Kwangju-Kun ■ Philippines: Baguio City ■ Singapore: Singapore ■ Sweden: Askim ■ USA: East Aurora (NY)