AC6305 AC6310

Compact in various circuit configurations

Description

A slip ring can be used in any electromechanical system that requires unrestrained, continuous rotation while transferring power and / or data from a stationary to a rotating structure. A slip ring is also called a rotary electrical interface, commutator, collector, swivel or an electrical rotary joint.

The AC6305 provides three, 5 amp circuits combined with 6, 9, or 12 signal (2 amp max) circuits. The AC6310 provides three, 10 amp circuits and 3 or 6 signal circuits. This compact power and signal handling design provides unique capability for many challenging applications.

Features

- 6, 9, 12 and 15 circuit models
- 5 amp / 2 amp and 10 amp / 2 amp circuit combinations
- Precision ball bearings meet or exceed life requirements for most commercial applications
- · Speeds up to 250 rpm
- · Compact size: 1.38 inch long
- Gold
- 12, 24, 36, 48 inch standard lead lengths (longer lead lengths are available)
- Sealed units are also available (dust and light splash only)
- Flexible silver-plated copper, color-coded, Teflon® insulated lead wires
- · Compatible with data bus protocols
- Also available with 6, 12, 18, and 24, 2 amp rings. Please refer to AC6023 data sheet.

Benefits

- · Smooth running
- Low torque
- Compact
- Very low noise (electrical)
- Quick shipment



Typical Applications


- CCTV pan / tilt camera mounts
- Electrical test equipment
- Manufacturing and process control equipment
 - Indexing tables
 - Robotics (end-effectors, arms, vision systems, sensors)
- · Exhibit / display equipment
- Medical equipment

Moog • www.moog.com

Specifications	AC6305	AC6310	Options
Operating Speed	250 rpm*	250 rpm*	Splash seals
Number of Circuits	3 @ 5 amps and 6, 9, or 12 @ 2 amps	3 @ 10 amps and 3 or 6 @ 2 amps	for dust and
Lead Lengths	12, 24, 36 and 48 inches	12, 24, 36 and 48 inches	moisture resistance • Metal housings with and without
Lead Size / Type	2 amp, 26 gauge silver plated copper, Teflon® 5 amp, 20 gauge silver plated copper, Teflon®	2 amp, 26 gauge silver plated copper, Teflon® 10 amp,16 gauge tin plated copper, Teflon®	
Voltage	240 VAC	240 VAC	flanges
Max Ambient Temp.	-40°C to +80°C	-40°C to +80°C	
Contact Material	Gold	Gold	
Current Rating	5 amps and 2 amps / circuit	10 amps and 2 amps / circuit]
Noise	60 milliohms max.	60 milliohms max.	

^{*}Please note that the operational life of the unit is dependent upon rotational speed, environment and temperature.

AC6305 Lead Wire Color Codes			AC6310 Lead Wire Color Codes						
	Ring #	Color Code	Ring #	Color Code		Ring #	Color Code	Ring #	Color Code
20 AWG	/ 1	BLK	9	GRN	16 AWG	/ 1	BLK	9	GRN
TAGGED	2	BLK	10	BLU	TAGGED	2	BLK		
LEADS	\ 3	BLK	11	VIO	LEADS	\ 3	BLK		
	4	BLK	12	GRY		4	BLK		
	5	BRN	13	WHT		5	BRN		
	6	RED	14	WHT-BLK		6	RED		
	7	ORN	15	WHT-BRN		7	ORN		
	8	YEL				8	YEL		




Dimensions in inches (millimeters)

AC6305 / AC6310 Dimensions

Moog www.moog.com REVISED 07/24 57

AC7551 Specifications (IP 65 Sealed Versions of AC6023, AC6305/AC6310, AC7188, & AC7203)		Options		
Operating Speed	250 rpm	No Flange		
Current Rating	2A, 5A, 10A	• 12, 24, 36, or 48 Inch Leads		
Voltage	240 VAC / VDC	See data sheets for standard circuit options AC6023		
Contact Material	Gold-on-gold	- AC6305/AC6310		
Temperature Range	-40°C to +80°C	- AC7188		
Electrical Noise	60 milliohms max.	- AC7203 - Custom wiring configurations can be quoted		
Video Connections	HD-SDI			
Ethernet Connections	10/100BaseT and 1000BaseT			

AC7551 Dimensions



Dimensions in inches

Part Number	Capsule Lenght (L)
AC7551-6	.965 in
AC7551-12	1.235 in
AC7551-18	1.505 in
AC7551-24	1.775 in

Dash Number	Dim "A"	Dim "B"
AC7551-*	12.0 in minimum	11.5 in minimum
AC7551-*A	24.0 in minimum	23.5 in minimum
AC7551-*B	36.0 in minimum	35.5 in minimum
AC7551-*C	48.0 in minimum	47.5 in minimum

Moog • www.moog.com REVISED 07/24 58