

## SRA-73526 / SRA-73528 / SRA-73599

*Compact in various circuit configurations*

### Description

A slip ring can be used in any electromechanical system that requires unrestrained, continuous rotation while transferring power and / or data from a stationary to a rotating structure. A slip ring is also called a rotary electrical interface, commutator, collector, swivel or an electrical rotary joint.

### Features

- 6, 12, 18 and 24 circuit models
- 2 amp / 240 VAC circuits
- Precision ball bearings meet or exceed life requirements for most commercial applications
- Speeds up to 250 rpm
- Compact size: .87 inch to 1.44 inch lengths (depending upon number of circuits)
- Gold-on-gold contacts
- Compatible with data bus protocols
- Flexible, color-coded, silver-plated, Teflon® insulated lead wires
- Transfers analog and digital signals

### Benefits

- Smooth running
- Low torque
- Compact
- Quick shipment



### Typical Applications

- CCTV pan / tilt camera mounts
- Electrical test equipment
- Manufacturing and process control equipment
  - Indexing tables
  - Robotics (end-effectors, arms, vision systems, sensors)
- Exhibit / display equipment
- Medical equipment

# Slip Ring Capsules (Compact)

## SRA-73526 / SRA-73528 / SRA-73599 Specifications

Operating Speed	250 rpm*
Number of Circuits	6, 12, 18, or 24
Lead Lengths	12, 24, 36 and 48 inches
Lead Size / Type	#26 AWG Teflon® insulated, stranded cond.
Voltage	240 VAC
Temperature Range	-40°C to +80°C
Contact Material	Gold
Current Rating	2 amps / circuit
Electrical Noise	60 milliohms max.


\*Please note that the operational life of the unit is dependent upon rotational speed, environment and temperature.

## Lead Wire Color Code

Ring#	Color Code	Ring#	Color Code	Ring#	Color Code
1	BLK	9	GRY	17	WHT-BLU
2	BRN	10	WHT	18	WHT-VIO
3	RED	11	WHT-BLK	19	WHT-GRY
4	ORN	12	WHT-BRN	20	WHT-BLK-BRN
5	YEL	13	WHT-RED	21	WHT-BLK-RED
6	GRN	14	WHT-ORN	22	WHT-BLK-ORN
7	BLU	15	WHT-YEL	23	WHT-BLK-YEL
8	VIO	16	WHT-GRN	24	WHT-BLK-GRN

Part Number	Length "L"	# of Circuits
SRA-73526-6	.57	6
SRA-73528	.76	12
SRA-73526-18	1.11	18
SRA-73599	1.24	24

## SRA-73526 / SRA-73528 / SRA-73599 Dimensions



Dimensions in inches