# **Fiber Optic Hybrid Units**

## SRA-73830-[ ]-JXX

Integrated slip ring and fiber optic rotary joint

### **Description**

A slip ring and Fiber Optic Rotary Joint (FORJ) can be used in any electromechanical system that requires unrestrained, continuous rotation while transferring power and data from a stationary to a rotating structure.

The SRA-73830-[ ]-JXX series provides a wide range of electrical connections, both power and signal, coupled with a singlemode or multimode FORJ to address todays increasing demand for reliable data transfer through a rotary interface. This design is well suited to applications where size is at a premium and reliability is a must.

The assembly provides a flange for convenient mounting of the stationary housing and drive pins to turn the rotating portion. Housing is plastic (standard) with aluminum and stainless steel options when required for a more demanding application.

### Slip Ring Features

- · Wide range of electrical options including:
  - Signal circuits handle up to 2 amps. Consult factory to discuss application
  - 100BaseT and 1000BaseT Ethernet
- · Multiple circuit configurations
- Compact
- Plug-and-play Ethernet
- Integrates capability of SRA-73683, SRA-73801 and SRA-73808 under one part number, plus 8 amp power capability
- · Can be integrated with a fiber optic rotary joint

### **FORJ Features**

- Provides rotary coupling for a multimode fiber link
- · Passive bidirectional device
- · Low cost, small size
- · Can be combined with our electrical slips and fluid unions
- Alternative drive coupling and mounting arrangements are available (consult factory for specification details)
- Can be integrated into existing slip ring designs
- Stainless steel or aluminum construction
- · Rugged design
- 90° fiber exits available for limited space requirements




### **Typical Applications**

- · Unmanned vehicles
- Robots
- Surveillance systems
- · Automated machinery



# **Fiber Optic Hybrid Units**

### SRA-73830-[ ]-JXX Dimensions




Part Number	"L"
SRA-73830-12	1.12 inch (28.4 mm)
SRA-73830-18	1.42 inch (36.1 mm)
SRA-73830-24	1.72 inch (43.7 mm)

For required electrical and fiber optic rotary joint features, please define the slip ring from data sheet SRA-73830 and FORJ from the table below. For additional details on the FORJ, please refer to FO285 / 286 data sheet.

A final configuration part number will be assigned by factory at time of order.

### SRA-73830-[ ]-JXX Part Numbering Scheme and FORJ Options



Specifications and information are subject to change without prior notice © 2016 Moog Inc. MS3268, rev. 2 03/20

#### **Americas**

1213 North Main Street Blacksburg, VA 24060 United States

Tel: +1 540-552-3011 Fax: +1 540-557-6400

### Asia-Pacific

Yokohama Nishiguchi KN Bldg. 10F 2-8-4 Kitasaiwai, Nishi-ku Yokohama, Kanagawa 220-0004 Japan

Tel: +81 45-328-1803 Fax: +81 45-328-1801

#### Europe

30 Suttons Business Park Reading, Berkshire RG6 1AW United Kingdom

Tel: +44 (0) 118-966-6044 Fax: +44 (0) 118-966-6524



www.moog.com

Email: contactus@moog.com