


## MODEL 8200

### STANDARD AND HIGH DEFINITION MINIATURE AUTOMATIC VIDEO TRACKER



The Model 8200 High Definition (HD) Standalone Miniature Automatic Video Tracker belongs to the latest tracker product family in Moog E-O Imaging's continued commitment to product innovation and improvement. This board is designed to allow complete interface customization to our customer's required applications. This is accomplished through the incorporation of the latest in digital signal processing (DSP) and field programmable gate array (FPGA) technology (providing a flexible architecture for customization). The Series 8000 Trackers can be interfaced with both analog and digital video sources, providing ease in interfacing with a wide variety of sensor systems. The analog video interface provides full 10-bit, 1024 gray level capability supporting both NTSC and PAL video formats. The 3G-SDI digital video interface supports standard and HD resolutions up to 1080p60 (SMPTE 259M/344M/292M/424M). The Model 8200

miniature tracker is designed to meet the demands of the surveillance and UAV markets for a low cost, high performance video tracker. Designed for standalone operation, the tracker operates from a single DC power supply accepting a wide input range from 6 to 28 volts.

*The Model 8201 tracker provides the same performance with a dual target capability.*

# MODEL 8200 STANDARD AND HIGH DEFINITION MINIATURE AUTOMATIC VIDEO TRACKER

## STANDARD FEATURES

- Algorithm Processing
  - Selectable Edge, Mass/Intensity Centroid, Vector\* and Correlation Algorithms
  - Multi-Target Detection and Acquisition
  - Robust Intrusion Detection, Coast and Target Recovery
- Control Interfaces
  - Gigabit Ethernet Interface (10/100/1000)
  - RS-232/422 Serial Communication Ports (4)
- Video Interfaces
  - Analog Video Input (1) and Output (1)
  - 3G-SDI Video Input (1) and Output (1)
- Standalone Operation
  - Single DC Power Supply
  - Complete Realtime System

- Integration
  - Advanced Motion Compensation (PID) Filter
  - Serial Control of Pan/Tilt and Servo Controller
  - Zoom Lens Scaling and Correction
  - Serial Control of Camera/Lens Systems (IR and Visible)
  - Serial Control of Laser Rangefinder
  - Interface to Remote Controller (Model 702 or 704)
  - Integrated Target Generator and Simulator
  - User-Controlled Text Annotation and Graphics
- Video Handling Capability
  - Interlaced and Progressive Formats
  - Resolutions up to 1080p60

## AVAILABLE OPTIONS

- Digital Video Configurations
  - 3G-SDI (up to 1080p60)
  - Camera Link (Base)
  - HDMI
- Video over Ethernet (compressed output)
- Remote Control Unit (Models 702 & 704)
- Environmentally-Ruggedized Camera System (Models 901 & 902)
- Custom Packaging and Form Factor
- Custom Algorithms / Symbology / Annotation
- Trajectory Simulation Capability
- Operator Training Capability
- Image Stabilization
- Image Fusion (IR and Visible)
- Simultaneous Multi-Target Tracking

## TYPICAL APPLICATIONS

- Surveillance
- Real Time Missile and Aircraft Tracking
- Weapon System Director
- Weapon System Evaluation
- Simulator Systems
- Trajectory Analysis
- Bomb and Weapons Scoring
- Image Matching
- Automated Calibration of Tracking Systems
- Laser System Alignment
- ECM Evaluation
- Spatial Measurement of Objects
- Re-entry Vehicle and Satellite Tracking
- Biomedical Analysis

## ELECTRICAL INTERFACES

- Video Interfaces (4)
  - Analog (CCIR, PAL, NTSC, RS-170), 1 in / 1 out
  - 3G/HD/SD-SDI (480i, 480p, 720p, 1080i, 1080p), 1 in / 1 out
- Optional Configurations (and other models)
  - 3G/HD/SD-SDI (480i, 480p, 720p, 1080i, 1080p)
  - Analog Video (CCIR, PAL, NTSC, RS-170)
  - Camera Link (Base)
  - HDMI (up to 2048 x 2048)

## SYSTEM CONTROL INTERFACES

- Serial Interfaces (4)
  - 115.2 kbps maximum (default)
  - Selectable RS-232/422
- Gigabit Ethernet Interface
  - Auto-negotiating 10/100/1000 Ethernet interface

## FUNCTIONALITY

- Tracking Algorithms
  - Mass Centroid
  - Intensity Centroid
  - Selectable Edge (top, bottom, left, right)
  - Correlation (Exhaustive Search)
  - Vector (Leading Edge) Track\*

- Tracking Gate Auto/Manual Size
  - Manual: adjustable from 1% to 90% of the field-of-view area in Edge and Centroid Modes
  - Adaptive: automatically adjusts to variations in target size
  - Correlation Mode: Reference area size from 8 x 8 up to 64 x 64 elements, independent horizontal and vertical size controls. Search area is 128 x 128 pixels/lines.
- Threshold (automatic/manual)
  - Allows identification of white and/or black targets or target gray levels
  - Automatic multi-gray level detection
- Automatic Coast Mode
  - Statistical Process determines the validity of the target
  - Optimal recovery from intrusions and disruption of track
- Reticle
  - Defines the AZ/EL null point of the system
  - User selectable reticle formats
- Display Symbology (customized to user requirements)
  - Tracking Gate Outline (Window/Corners)
  - Reticle (Crosshair)
  - Track Point Indicator (Flag/Crosshair)
  - Offset Track Point
  - Threshold Enhancements (Highlighted Target Data)
  - Characters for displaying system status and mode information
  - Alphanumeric generator for user-defined messages

- Graphical User Interface
  - PC-based program for setup and testing through the RS-232/422 or Ethernet interface
- Built-In-Test
  - Performs end-to-end testing
  - Verifies all track modes
- Field Downloadable Software Updates (DSP/FPGA)
- Sophisticated PID Filter
- Configuration Save Capability
  - Stores up to 10 user-defined configurations in FLASH
  - Allows user to define Tracker boot-up configuration
- Embedded Motion Control Processor

## PHYSICAL SPECIFICATIONS

- Board Dimension
  - 4.5 inches x 5.0 inches (11.4 cm x 12.7 cm)
  - Conformal coated per MIL-I-46058
- Temperature Range
  - Operating: -40° to +85°C
  - Storage: -40° to +85°C
- Relative Humidity
  - 0 to 95% non-condensating
- Power
  - +6 to +28 VDC
  - 12 watts (nominal)

\* Vector Track mode is only available with mount position feedback

# EQUIPPING THOSE WHO DEFEND FREEDOM

# MOOG

+1 321.435.8722 | [www.moog.com/videotracking](http://www.moog.com/videotracking) | [videotracking@moog.com](mailto:videotracking@moog.com)



MoogSpace and Defense



@MoogSDG



@MoogSDG



@MoogSDG



@MoogInc

Equipment described herein falls under the jurisdiction of the ITAR and requires US Government Authorization for export purposes. Diversion contrary to US law is prohibited.

© 2021 Moog, Inc. All rights reserved.  
Product and company names listed are trademarks or trade names of their respective companies.

Specifications subject to change without notice.  
Consult factory for latest specifications and available options.

Form 500-1220 07232021