



Credit: U.S. Army/Maj. Robert Fellingham



Credit: MAG Aerospace



*Credit: U.S. Army National Guard/
Staff Sgt. Gabriel Rivera*



Credit: U.S. Navy

MISSION CRITICAL DEFENSE SOLUTIONS

EQUIPPING THOSE WHO DEFEND FREEDOM

MOOG DEFENSE
EQUIPPING THOSE WHO DEFEND FREEDOM
ACROSS MULTI-DOMAIN OPERATIONS



LAUNCH VEHICLES

- Power & Control Electronics
- Thrust Vector Control Systems
- Chemical & Cold Gas Engine Systems
- Main Engine Fluid Controls
- Secondary Payload Adaptors & Delivery Systems
- Vehicle SoftRide® Isolation

SPACECRAFT &
PAYLOAD DELIVERY SYSTEMS

- Propulsion Systems
- Integrated Flight Avionics
- Structures & Isolation Solutions
- On-board Mechanisms & Control Electronics
- Spacecraft Bus Solutions



ROTARY WING

- Weapon Stores Management Systems (SMS)
- Missile Launchers & Simulators
- Flight Control Systems
- Vibration Control
- Slip Rings
- Cockpit Avionics Solutions



FIXED WING

- Weapon SMS
- Flight Control Systems
- Motion Control for ISR Search Radar
- Stabilized Motion Control for Turrets
- Engine Control Systems
- Media Converters/Ethernet Switches
- Missile Launchers & Simulators
- Cockpit Avionics Solutions



MISSILES &
KILL VEHICLES

- Thrust Vector Control
- Fin Control
- Wing Deploy
- Integrated Propulsion Systems & Fluid Control
- Seeker Motors
- Avionics & Sensor Integration
- Structures & Isolation Solutions
- Control Electronics



UAS

- Flight Control Systems
- Weapon SMS
- Missile Launchers & Simulators
- Actuators
- Vehicle Management Systems



RADAR

- Radar Multi-Axis Positioning Systems
- Cooling Equipment Units
- Slip Rings
- Digital Airfield Solutions
- Runway FOD Detection



COMBAT &
TACTICAL VEHICLES

- Reconfigurable Integrated-weapons Platform
- Turret Weapon Systems & Integration
- Stabilized Motion Control
- Fire Control
- Ammunition Handling
- Large Caliber Weapon Control Systems
- Modular Countermeasure Directors
- Multi-Mission Payload Systems
- Short Range Air Defense
- C-UAS Solutions



LAUNCHERS

- EH to EM Conversions & Upgrades
- High Voltage Elevation & Azimuth Control
- Directed Energy
- Weapon SMS
- Slip Rings



SURFACE
VESSELS

- EM Actuation
- Weapon SMS
- Stabilized Motion Control for Turrets
- Gun Control Units
- Active Stabilization
- Ammunition Handling



AUV / UUV

- Propulsion Systems
- Steering & Dive Control Systems
- Subsea Utility Motors



SUSTAINMENT SERVICES

- OEM Product Support
- Modernization & Upgrades
- Service & Support
- Training
- Engineered Solutions

SUBMARINES

- Valve Actuation
- Hull Mechanical Actuation
- Servo Valves
- Torpedo Steering
- Periscope Actuation
- Optronics Rotary Joints



SPACE

LEO/MEO/GEO & Beyond
DOD
Commercial
Civil

ROTARY
WING

Black Hawk
V-22
Seahawk
S-92 | S-76
AW129 | AW159
FLRAA
MD 530F
Bell 407
AH-64E Apache
AH-530

FIXED
WING

F-15, F-16, F-18, F-35
AC-130J Ghost Rider
Caravan
Eurofighter
AT-802/OA-1K
MC-145B
Scorpion
Bronco II
PredSR
KF-21 Boramae
T-50 Golden Eagle

MISSILES &
KILL VEHICLES

Tactical & Strike Systems
Hypersonic Missile Systems
Long Range Ballistic Missiles
Air & Missile Defense

UAS

Predator
Gray Eagle
MQ-25

RADAR

G/ATOR
AN/TPY2
Sentinel
AN/TPQ-53
MEADS
Aegis
TRML-4D

COMBAT &
TACTICAL VEHICLES

M-SHORAD
LAV-AT/25
Stryker
CV90
PZH 2000
Bradley
MLIDS
Abrams
M113AS4
RCH 155
CWS-Heavy
Ariete C2
Centaurus II
Jaguar
Piranha V
CASEAR 155
K9 Thunder SPH
K9 Vajra Howitzer
K21 IFV
K2 Black Panther

LAUNCHERS

MML
HIMARS
MLRS

SUBMARINES

Seawolf Class
Virginia Class
Ohio Class
Columbia Class
Collins Class
Scorpene Class
Dreadnought Class
Barracuda Class
Mark 48 Torpedo
Mk54 Torpedo

SURFACE
VESSELS

Ford-class Aircraft Carrier
Littoral Combat Ship
Frigate Types 45/23/122-125
K30
Nimitz Class Carriers
Chevallier CT40 c-UAS
Evolved Cape Class Patrol Boat
Hobart Class Destroyer

AUV / UUV

XLUV
UUV-FoS
Echo Ranger
Echo Voyager
CLASSIFIED
RMMV

SPACE

AIR

LAND

SEA

MULTI-DOMAIN SUSTAINMENT SERVICES

CAPABILITIES

EXPERIENCE

AIR

MISSILE CONTROLS

From tactical to strategic missiles, from close air support to long range hypersonic, Moog leads the industry in providing precision flight control actuation systems and thrust vector control.

MOOG CAPABILITIES

- Actuation and control electronics
 - Thrust vector control
 - Fin control
 - Wing deploy mechanisms
 - Fin lock and deploy solutions
- Integrated propulsion systems and fluid control systems
 - Liquid and cold gas propulsion
 - Kill vehicle and booster propulsion components
- Avionics and sensor integration
- Structures and shock/vibration isolation solutions
- Integrated, additively manufactured structures
- Power distribution and management
- Arm/disarm switches
- Seeker motors, resolvers, and slip rings

TACTICAL THEATER AND LONG RANGE MISSILE PLATFORMS

- HELLFIRE • Tomahawk
- TOW

INTERCEPTOR AND KILL VEHICLE STEERING

Today's sophisticated Ballistic Missile Defense (BMD) Systems rely on Divert and Attitude Control Systems (DACS) to steer the Kill Vehicle (KV) through the final intercept trajectory. At the heart of the DACS are Moog thruster valves which precisely meter the flow of propellant and oxidizer to the rocket engines used for KV steering.


Solid fueled DACS utilize lightweight, high bandwidth actuators to throttle and control rocket motor thrust. Moog's electro-mechanical and hydraulic actuation systems can be customized to the challenging envelope and environmental requirements for pintle actuation applications.

DIVERT AND ATTITUDE CONTROL SYSTEMS (DACS) EXPERIENCE

- Thruster valves • Service valves
- Regulators • Tanks

MAJOR INTERCEPTOR PLATFORMS

- Patriot • NGI
- THAAD



TACTICAL CONTROL ACTUATION SYSTEM



LONG RANGE FIN AND WING DEPLOY ACTUATION



SUPERSONIC CONTROL ACTUATION SYSTEM



HYPERSONIC CONTROL ACTUATION SYSTEM



PROPULSION MODULES



PINTLE ACTUATOR



THRUSTER VALVES



REGULATORS



SERVICE VALVES



PROPELLANT TANKS

AIR (CONTINUED)

WEAPON STORES MANAGEMENT SYSTEMS (SMS)

The Third Generation Weapon Stores Management System (SMS) is a Modular Open System Approach (MOSA) compliant COTS weapons control system that seamlessly integrates with aircraft sensors and mission management systems to provide the crew with a superior fire-control solution.


This proven, lightweight rugged system is an affordable solution to stores management on air, land and sea platforms. The SMS leverages Moog's extensive experience in systems integration, internal software development, weapons technology, and fire control solutions. SMS software is approved as non safety-critical DO-178C DAL E.

The flexible modular design of the SMS enables fast delivery, rapid integration and future upgrades to the sensors, avionics and weapons ensuring the SMS's value for future mission requirements and weapon systems expansion including Universal Armament Interface (UAI).

Additionally, Moog offers a Missile Simulator (MSL SIM) with a flightworthy rail-mount design that simulates different types of AGM-114 HELLFIRE® missiles.




BLACK HAWK
PLATFORM
SMS INTEGRATION



WEAPON SMS
ON AT-802/OA-1K SKY WARDEN

MOOG'S LIGHTWEIGHT DUAL
RAIL LAUNCHER (DRL) WITH
HELLFIRE INTERFACE UNIT
[46 LBS.]

DIGITAL SMS COMPONENTS




LAND

RECONFIGURABLE INTEGRATED-WEAPONS PLATFORM (RIwP®)

RIwP is an innovative, multi-domain remote weapons platform offering unmatched capacity and capability. Multiple weapon options and in-field weapon reconfigurability guarantee tailored overmatch in every combat situation. Engineered with many advanced features, RIwP includes high-performance target acquisition technology and world-class pointing/stabilization accuracy. This ensures U.S. and allied forces see first, engage first and achieve mission success. Designed to be weapon, sight, and platform agnostic RIwP accommodates firepower growth to support mission requirements. With survivability in mind the turret allows the warfighter to reload under armor.

RIwP offers air defense, anti-armor, or multi-mission capabilities via medium caliber and indirect fires, available in various configurations. RIwP can be utilized on medium-sized platforms such as wheeled/tracked armored fighting vehicles, robotic combat vehicles, and containerized platforms.



LAND (CONTINUED)

WEAPON SMS

In addition to being at the heart of the FMP solution, Moog's Weapon SMS is customizable for air, land, and sea applications. Successful test fires have been conducted from trailers, and military vehicles. SUVs and vans can also be weaponized.


(see more on Moog's proven Weapon SMS solution for air platforms on pages 6 and 7)



FLEXIBLE MISSION PLATFORM (FMP™)

The Flexible Mission Platform is a payload, mission, and platform agnostic system. FMP allows users to host the weapon, sensor, or other mission package of their choice from the vehicle, ship, container, or trailer of their choice.

FMP is built around Moog's world-renowned military motion control technology. Options include integration of Moog's high-performance stabilization and weapon stores management systems (SMS), providing missile firing capability to suit any mission.



LAND (CONTINUED)

TURRETED WEAPON SYSTEMS

Moog designs, manufactures and integrates weapon systems, sub-systems and products for a variety of global military vehicle platforms. You can gain access to the expertise in fire control, gun control, weapon stabilization, and weapons integration found on over 30 of the world's leading military vehicle platforms including manned and unmanned turrets and remote weapon stations. Small, (e.g. 12.7mm) medium (e.g. 30mm) and large caliber (e.g. 155mm) weapons are equally supported by Moog technology.




SUBSYSTEMS



EXPEDITIONARY RADAR DEPLOYMENT SYSTEMS

Moog provides motion control products, integrated subsystems, and complete single and multi-axis actuation systems for land radar platforms, including:

- Antenna elevation and fold actuation
- Point and stare actuation
- Azimuth drive motor, controller, actuation
- Automatic leveling actuation
- Integrated rotary joint assembly
- Hydraulic to electric conversions
- Communication networking products





LAUNCHERS, OEM, AND CONVERSIONS AND UPGRADES

Moog is an OEM for existing and future launcher programs providing elevation and azimuth precision control as well as power and data transmission. Moog also works closely with vehicle manufacturers and the armed forces to upgrade, convert, and reset existing assets. Our modeling, hardware, software, mechanical and production engineering teams are experts in both electromechanical (EM) and electrohydraulic (EH) motion control systems and technologies, providing system upgrades to meet strict space, weight, and power constraints. We have developed patented high-redundancy, fail-safe, EM actuation systems offering users reassurance in power failure conditions.




ELECTRIC MODULAR ACTUATOR AND CONTROLLER (MAC)

Driven by the need to reduce crew fatigue, increase reliability, enhance performance, and purchase with green/sustainability in mind, many of the low power and less complex functions in modern defense platforms are moving from traditional manual, pneumatic, or hydraulic control to electric actuation. Whether considering rotary or linear actuation, the Moog MAC family is designed to meet the required levels of reliability and affordability, as well as the rigorous demands of shock, vibration and EMC.

Comprised of a range of low power motors and actuation systems available with optional embedded electronic controls which can be applied to variety of applications such as:


- Antenna elevation and fold actuation
- Missile pod movement
- Travel lock
- Gun cocking
- Ammunition bunker doors
- Sight protection covers
- Ammunition handling mechanisms



The MAC design is based on a set of building blocks that allow flexibility of implementation and application and also offers the platform manufacturer an element of consistency from one, two, or even more axes of control. With typical powers from 50w to 1kw, the newly developed MAC builds on Moog Defense Systems' heritage of our more complex systems, but packaged in a simple, rugged, easy to use format.

RADAR COOLING EQUIPMENT

Our line of brushless DC fan motors provide extremely reliable cooling for critical defense radar equipment. As a crucial element of U.S. national missile defense, such systems operate in some of the harshest environments on earth, and when called upon absolutely must function as designed every single time. Moog provides greatly enhanced manufacturability, reliability and performance to this mission essential equipment. We also supply associated electronic controls for cooling systems, providing a complete turnkey solution to the customer.



FAN MOTOR



CONTROLLER AREA NETWORK SPLITTER




CONTROLLER

SURFACE SHIP WEAPONS SYSTEMS

Moog is a leading supplier delivering high-precision motion control and electronic solutions to many of the world's naval forces.

Comprehensive systems are engineered to perform reliably in the harshest of marine environments, providing the long-life and dependability our customers require. Extending our customers' investments even further is the scalability and upgradeability designed into every component and system along with through life support. Many of Moog's precision technologies are integrated into littoral and blue water ships. On-board these ships, Moog's premier electromechanical turret drive actuation, stabilization and slip ring technologies are incorporated into various weapon platforms. Moog provides hydraulic throttle control servo-actuators, electromechanical actuators (EMA), and direct drive valves (DDV) on arresting gear for aircraft landing.

Moog actuation is also found in mission critical surface ship applications such as the propulsion plants of both USS Nimitz and USS Gerald R Ford-class aircraft carriers.



MULTI-AXIS AMMUNITION HANDLING

Moog heritage is responsible for the design, manufacture and integration of precision ammunition handling systems for a variety of applications including naval gun ammunition. Our ammunition handling systems involve complex mechanical integration, linear and rotary actuation and sophisticated, ruggedized motor control technologies.



BAE Systems' Mark 8 Mod 1 Naval gun: Moog provides the high performance motors for aiming stabilization and ammunition loading. The slip ring transfers power and data.

Rheinmetall's MLG27 naval gun mount: Moog provides the electric gun /turret drives, motion sensors along with the power and stabilization electronics. The slip ring transfers power and data.




SEA (CONTINUED)

Moog is a major supplier of hydraulic, electromechanical and pneumatic motion control systems for submarines, aircraft carriers, and other naval vessels. The company has designed and manufactured hundreds of critical control systems that operate valves, open and lock hatches and provide propulsion for these platforms.

SUBMARINE ACTUATION


Moog’s legacy supplying actuation in U.S. Navy submarines extends more than 50 years, from the George Washington-class to the Columbia-class, including hydraulic steering controls for the MK48 torpedo.

Additionally, Moog supplies critical components to other naval customers across the globe. These programs include the French Barracuda-class, United Kingdom Dreadnaught-class, and the Australian Collins-class submarines.



AUTONOMOUS UNDERSEA VEHICLE PROPULSION AND CONTROLS

For ROV and AUV platforms Moog provides motors, controllers, actuators, servovalves, and other equipment. We are making investments in future technologies to support these platforms. Moog facilities in the United States, Canada, Germany, Australia, and the United Kingdom are dedicated to the marine and naval industries. If your application is in a challenging environment where performance really matters, Moog has the reliable, low-risk solution to ensure mission success and provide propulsion for these platforms.



DEFENSE PRODUCTS



ROTARY JOINTS AND SLIP RINGS

These high performance products are used in systems that require unrestrained, continuous rotation while transmitting power, data and media from a stationary device to a rotating structure. High bandwidth options include Ethernet, high definition video and other industry standard formats. Moog also has solutions including fiber optic rotary joints, fluid rotary unions and position sensors.



DIRECT DRIVE DC TORQUE MOTORS AND ALTERNATORS

Frameless torque motors are used in defense applications that require high power density and quick accelerations. The motors are optimized to minimize input power for maximum efficiency. Alternators in the same mechanical configuration can be used for mobile power generation.



RESOLVERS

Moog offers rugged resolvers that provide accurate positioning and velocity feedback, as well as commutation of brushless motors. These models withstand the shock and vibration levels often encountered in aerospace and military applications. They are used for vertical integration with motors and slip ring assemblies.



ACTUATORS

Multi-purpose actuators are available in both rotary and linear configurations and are standard building blocks in a variety of systems. Some of our actuators integrate servo electronics. These actuators are used on air, ground and unmanned applications.

HIGH SPEED DATA COMMUNICATIONS

Moog provides innovative components and communication sub-systems for both copper and optical fiber based systems used in harsh environments. Moog meets the demanding high speed and secure networking equipment requirements of todays modern defense systems. The product range includes electro-optical transceivers, link extenders, Ethernet media converters and switches, data aggregators and multiplexer/ de-multiplexer solutions.



INTEGRATED MOTION ASSEMBLIES

Our higher level solutions range from simple combinations of individual products to sophisticated electromechanical assemblies including the motor, drive electronics, slip rings, fiber optic rotary joints, fluid/pneumatic swivels and RF rotary joints. Moog's single-axis gimbal stage supports most payloads, and all the rotary components are integrated into one assembly. This design reduces set-up time and simplifies the installation process.



MOOG TOTAL SUPPORT OFFERINGS

Our comprehensive global sustainment program broadly includes OEM product support, modernization and upgrades, service and support, training and Engineered Solutions supporting industry's wide range of defense products across multi-domain operations. As an OEM supplier, Moog is the logical choice for follow-on product support.

OEM PRODUCT SUPPORT

- Spares
- Repair and overhaul
- Software support – revision changes, etc.
- Parts and kits
- Logistics




MODERNIZATION AND UPGRADES

- Upgrades
- Obsolescence management
- Additive manufacturing

SERVICE AND SUPPORT

- Public-Private Partnerships (P3)
- OEM employed Field Service Reps (FSR)
- Joint venture experience
- Licensing
- Data – technical information, drawings
- Documentation



TRAINING

- Maintenance
- Operators/Operations
- Simulation
- Subsystem integration
- Theory of operation
- Test equipment
- Training support



ENGINEERED SOLUTIONS

- Reverse engineering
- Repair and overhaul of non-Moog hardware
- Tech insertion
- Additive manufacturing



EQUIPPING THOSE WHO DEFEND FREEDOM

MOOG | Shaping the way our world moves™

AMERICAS
defense@moog.com
www.moog.com/defense



Moog Space and Defense

AUSTRALIA
Info.australia@moog.com
www.moog.com.au



Moog Inc.



@Moog_Inc

EUROPE
defenceeurope@moog.com
www.moog.com/defence



@Moog.Inc

The appearance of U.S. Department of Defense (DoD) visual information does not imply or constitute DoD endorsement.
Some of the Products and Solutions shown in this brochure may be subject to the export control requirements of the country in which they are manufactured. Contact Moog for additional information.

© 2024 Moog, Inc. All rights reserved.
Product and company names listed are trademarks or trade names of their respective companies.