

RECONFIGURABLE ACTUATION CONTROL UNIT FAMILY (RACU)



Moog has developed a line of actuation control solutions that are designed to be used in multiple aerospace and harsh environments. The commercial actuation controllers fall into our Reconfigurable Actuation Control Unit (RACU) product family. This family is capable of covering a wide range of performance characteristics with varying design parameters. This new product line is derived and based on existing and qualified Moog heritage solutions

that is specifically focused on lower cost, faster lead times, and a reconfigurable nature. The modularity and availability of the controllers lends itself to both rapid design iteration and solution evolution.



RECONFIGURABLE ACTUATION CONTROL UNIT FAMILY (RACU)

PERFORMANCE SPECIFICATIONS



Features	Low Power RACU	Medium Power RACU	High Power RACU
Processing Element	FPGA w/ onboard memory for reliable high speed loop closure	FPGA w/ onboard memory for reliable high speed loop closure	FPGA w/ onboard memory for reliable high speed loop closure
Motor control type	3-phase brushless DC	3-phase brushless DC	3-phase brushless DC
Motor control axes	2	2	2
Input Power	28 VDC	28 VDC	28 VDC
Bus Power	N/A (derived from 28 V input)	Up to 450 VDC	Up to 450 VDC
Peak Motor Phase Current	35 ADC	120 ADC	400 ADC
Integral Regenerative Energy Dissipation	Yes	No (regen should be dissipated external to controller)	No (regen should be dissipated external to controller)
Input Command	RS-422 or Analog	RS-422 or Analog	RS-422 or Analog
Motor Commutation Feedback Sensors	Sensorless, HEDs, Resolver, Rotary Encoder	Sensorless, HEDs, Resolver, Rotary Encoder	Sensorless, HEDs, Resolver, Rotary Encoder
Output Sensors	Motor counting, RVDT/LVDT, Linear /Rotary Encoder	Motor counting, RVDT/LVDT, Linear /Rotary Encoder	Motor counting, RVDT/LVDT, Linear /Rotary Encoder
User Programmable Gains	Yes (Moog support also available)	Yes (Moog support also available)	Yes (Moog support also available)
Aerospace environments	Yes	Yes	Yes
Temperature Range	-40C to +105C	-40C to +105C	-40C to +105C
EEE Part Grade	Class III (Enhanced plastic / automotive or otherwise upscreened plastic parts)	Class III (Enhanced plastic / automotive or otherwise upscreened plastic parts)	Class III (Enhanced plastic / automotive or otherwise upscreened plastic parts)
Dimension Estimate	9.5 in x 6 in x 1.3 in	10.25 in x 10.5 in x 2.1 in	15 in x 10 in x 2.75 in
Weight	2.6 lb	9.0 lb	15.5 lb

MOOG
SPACE AND DEFENSE GROUP

Patrick Biver - Business Development
+1.716.248.0112
pbiver@moog.com



MoogSpace and Defense



@MoogSDG



@MoogSDG



@MoogSDG



@MoogInc

Equipment described herein falls under the U.S. Export Administration Regulations and is subject to licensing requirements under either the ITAR or the EAR.

© 2021 Moog, Inc. All rights reserved.
Product and company names listed are trademarks or trade names of their respective companies.

Form 500-1306 1021